

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [29-11-0122](#)
Status: **Active**
Overview: [SPOX™ Wire-to-Board Connectors](#)
Description: 2.50mm Pitch SPOX™ Wire-to-Wire Plug Housing, Friction Lock, Optional Mounting Ears, 12 Circuits

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-5102-003 \(PDF\)](#)
[Product Specification PS-51191-003 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
TUV R72090224
UL E29179

General

Product Family Crimp Housings
Series [5240](#)
Application Signal, Wire-to-Wire
Overview [SPOX™ Wire-to-Board Connectors](#)
Product Name SPOX™
UPC 800754386500

Physical


Circuits (maximum) 12
Flammability 94V-0
Gender Male
Glow-Wire Compliant No
Lock to Mating Part Yes
Net Weight 2228.200/mg
Number of Rows 1
Packaging Type Bag
Panel Mount No, Yes
Pitch - Mating Interface 2.50mm
Stackable No
Temperature Range - Operating -40°C to +105°C

Material Info

Old Part Number 5240-12

Reference - Drawing Numbers

Product Specification PS-5102-003, PS-51191-003
Sales Drawing SD-5240-001



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[5240Series](#)

Mates With
[51191](#) Housing

Use With
[5241](#)