



MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF

Ø.139 MAX ON 1.000±.002 CENTERS

2 - SEALED CONSTRUCTION PROVIDES SPLASH RESISTANCE

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.		THIRD ANGLE PROJECTION 	
CHARACTERISTICS		ELECTRICAL DATA	
OPERATING FORCE ----- 3 1/2 OZ MAX		CONTACT ARRANGEMENT S P D T	
RELEASE FORCE ----- 3/4 OZ MIN		L96 15A 125, 250 OR 480 VAC 1/8HP 125 VAC, 1/4HP 250 VAC 1/2A 125 VDC, 1/4A 250 VDC	
DIFFERENTIAL TRAVEL ----- .004 - .040		CE 	
OVERTRAVEL ----- .156 MIN		L288 L599 L306 16A 250V ~ T85 5E4	
CHECK 24JAN02		SCALE FULL DO NOT SCALE PRINT UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±	
GRT		WEIGHT .076 LB	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[BZ-2RW8055520T](#)