

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY

Sensor, thermocouple, Stainless Steel 310. Type K, Mineral Insulated,
1.0, 1.5, 3.0, & 6.0mm Diameters



- Mineral insulated K thermocouples
- Very rugged and flexible
- Stainless steel (310) Sheath
- Particularly suitable for high pressure, high vacuum or high vibration applications
- Max temperature of probe 1100°C (K)
- Plain pot seal (max temp 200°C)
- 7/0.2mm PFA Insulated Lead 2mt Long

Dimensions		Farnell code	LAB code	Lab Data Ref	Lab Stock Code
Probe Dia	Probe Length				
mm	mm				
1.0	100	TBA	MA-ISK-S10-100-P1-2.0-C2-T	FAR54/A	XF-434-D
1.0	150	TBA	MA-ISK-S10-150-P1-2.0-C2-T	FAR54/B	XF-435-D
1.0	250	TBA	MA-ISK-S10-250-P1-2.0-C2-T	FAR54/C	XF-436-D
1.0	500	TBA	MA-ISK-S10-500-P1-2.0-C2-T	FAR54/D	XF-437-D
1.0	1000	TBA	MA-ISK-S10-1000-P1-2.0-C2-T	FAR54/E	XF-438-D
1.5	100	TBA	MA-ISK-S15-100-P1-2.0-C2-T	FAR54/F	XF-439-D
1.5	150	TBA	MA-ISK-S15-150-P1-2.0-C2-T	FAR54/G	XF-440-D
1.5	250	TBA	MA-ISK-S15-250-P1-2.0-C2-T	FAR54/H	XF-441-D
1.5	500	TBA	MA-ISK-S15-500-P1-2.0-C2-T	FAR54/I	XF-442-D
1.5	1000	TBA	MA-ISK-S15-1000-P1-2.0-C2-T	FAR54/J	XF-443-D
1.5	2000	TBA	MA-ISK-S15-2000-P1-2.0-C2-T	FAR54/K	XF-444-D
3.0	100	TBA	MA-ISK-S30-100-P1-2.0-C2-T	FAR54/L	XF-445-D
3.0	150	TBA	MA-ISK-S30-150-P1-2.0-C2-T	FAR54/M	XF-446-D
3.0	250	TBA	MA-ISK-S30-250-P1-2.0-C2-T	FAR54/N	XF-447-D
3.0	500	TBA	MA-ISK-S30-500-P1-2.0-C2-T	FAR54/O	XF-448-D
3.0	1000	TBA	MA-ISK-S30-1000-P1-2.0-C2-T	FAR54/P	XF-449-D
3.0	2000	TBA	MA-ISK-S30-2000-P1-2.0-C2-T	FAR54/Q	XF-450-D
6.0	100	TBA	MA-ISK-S60-100-P1-2.0-C2-T	FAR54/R	XF-451-D
6.0	150	TBA	MA-ISK-S60-150-P1-2.0-C2-T	FAR54/S	XF-452-D
6.0	250	TBA	MA-ISK-S60-250-P1-2.0-C2-T	FAR54/T	XF-453-D
6.0	500	TBA	MA-ISK-S60-500-P1-2.0-C2-T	FAR54/U	XF-454-D
6.0	1000	TBA	MA-ISK-S60-1000-P1-2.0-C2-T	FAR54/V	XF-455-D
6.0	2000	TBA	MA-ISK-S60-2000-P1-2.0-C2-T	FAR54/W	XF-456-D

Data Ref: FAR 54