


AVEN

*High Performance Precision Tools and Optical Inspection Systems
for Industrial, Scientific and Research Applications*

[Home](#) | [My Account](#) | [Sh](#)
[Catalogs & Sales Info](#)
[All Products Listing](#)
[Find A Distributor](#)
[Find A Sales Rep](#)

Wednesday, January 28th, 2009

Come and see Aven at MDM West, February 10-12, 2009 at the Ana

DSZT-70 20x-70x Stereo Zoom Body


[larger image](#)

The DSZT-70 Series body can be mounted on a variety of boomstands. You choose the rack & pinion focus mount, illumination, and accessories to meet your specific requirements. Various eyepieces & auxiliary lenses can be used for desired magnification and working distance. Please see our downloadable PDF document below for optical data on the DSZ-Series Microscopes.

- 10x Wide Field eyepieces (field number 20)
- Rubber eye guards
- Dust cover
- For high magnification applications
- Zoom Ratio of 3.5: 1
- Total Magnification from 20x to 70x
- Field of View of 10mm to 2.8mm (0.39" to 0.11")
- Working distance 80mm (3.15")
- Magnification range of 5x to 224x with optional lenses

* Note specification mentioned above are with Wide Field 10x eyepieces.

From the options listed below you choose:

1. Focus Mount
2. Stand
3. Illumination
4. CCD Camera
5. CCD Camera Adapter-please note, if you have chosen a CCD Camera, you will need the adapter!
6. LCD Monitor
7. Auxiliary Lenses
8. Eyepieces

****Please note-0.5x Auxiliary Lens cannot be used with stands T and TL.****