




REV. 0
DCO 16817


COIL: @ 25°C
RESISTANCE 1620 OHMS ± 10%
NOMINAL VOLTAGE 30.0 VDC
MUST OPERATE 14.3 VDC
MUST RELEASE 1.4 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 2500 CPS @ 20 g's
SHOCK 50 g's 6 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 6 MS MAX.
RELEASE 5 MS MAX.
CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO
2 AMPS 28 VDC RESISTIVE
100,000 OPERATIONS

DR. PBB 2/12/01 CK. TLG 02-12-01

CII Technologies
advanced control electronic solutions

CUST. C.I.I. STD. "HMS" RELAY
CUST. NO. REV.

HMS1201S005