





## .070 MULTILOCK Connectors

### Tab Contact

| Contact                                                                                                                                                                                                | Wire Range                             | Wire Ins. Diameter | Material/Finish | Part No. |                 |          |                 | Hand Tool No.<br>(Instruction Sheet) |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------|--------------------|-----------------|----------|-----------------|----------|-----------------|--------------------------------------|
|                                                                                                                                                                                                        |                                        |                    |                 | S.T.     |                 | L.P.     |                 |                                      |
|                                                                                                                                                                                                        |                                        |                    |                 | Brass    | Phosphor Bronze | Brass    | Phosphor Bronze |                                      |
| <div>.070Tab(For Cap)</div> <div></div> <div>Crimp Specifications:114-5092</div>                                      | 0.2~0.3mm <sup>2</sup><br>(AWG#24-22)  | Ø1.4-1.9mm         | Pre-tin         | 173633-1 | 173633-2        | 175029-1 | 175029-2        | 91580-1<br>(411-5481)                |
|                                                                                                                                                                                                        |                                        |                    | Sel. Gold       | —        | 173633-3        | —        | 175029-3        |                                      |
|                                                                                                                                                                                                        | 0.5~1.25mm <sup>2</sup><br>(AWG#20-16) | Ø2.0-2.6mm         | Pre-tin         | 173645-1 | 173645-2        | 175030-1 | 175030-2        | 91573-1<br>(411-5480)                |
|                                                                                                                                                                                                        |                                        |                    | Sel. Gold       | —        | 173645-3        | —        | 175030-3        |                                      |
| <div>.070Tab(For Cap)</div> <div></div> <div>For an extra-thin jacketed cable<br/>Crimp Specifications:114-5157</div> | 0.3~0.5mm <sup>2</sup><br>(AWG#22-20)  | Ø1.0-1.5mm         | Brass/Pre-tin   | 175207-1 | —               | —        | —               | —                                    |
|                                                                                                                                                                                                        | 0.5~1.25mm <sup>2</sup><br>(AWG#20-16) | Ø1.2-2.2mm         | Brass/Pre-tin   | 175208-1 | —               | —        | —               | —                                    |

### Receptacle Contact

| Contact                                                                                                                            | Wire Range                             | Wire Ins. Diameter | Material/Finish | Part No. |                 |          |                 | Hand Tool No.<br>(Instruction Sheet) |
|------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------|--------------------|-----------------|----------|-----------------|----------|-----------------|--------------------------------------|
|                                                                                                                                    |                                        |                    |                 | S.T.     |                 | L.P.     |                 |                                      |
|                                                                                                                                    |                                        |                    |                 | Brass    | Phosphor Bronze | Brass    | Phosphor Bronze |                                      |
| <div>.070Receptacle(For Plug)</div> <div></div> | 0.2~0.3mm <sup>2</sup><br>(AWG#24-22)  | Ø1.4-1.9mm         | Pre-tin         | 173630-1 | 173630-6        | 175026-1 | 175026-6        | 91580-1<br>(411-5481)                |
|                                                                                                                                    |                                        |                    | Sel. Gold       | 173630-2 | 173630-7        | 175026-2 | 175026-7        |                                      |
|                                                                                                                                    | 0.5~1.25mm <sup>2</sup><br>(AWG#20-16) | Ø2.0-2.6mm         | Pre-tin         | 173631-1 | 173631-6        | 175027-1 | 175027-6        | 91573-1<br>(411-5480)                |
|                                                                                                                                    |                                        |                    | Sel. Gold       | 173631-2 | 173631-7        | 175027-2 | 175027-7        |                                      |
| Crimp Specifications:114-5091                                                                                                      |                                        |                    |                 |          |                 |          |                 |                                      |
| <div>.070Receptacle(For Plug)</div> <div></div> | 0.3~0.5mm <sup>2</sup><br>(AWG#22-20)  | Ø1.0-1.5mm         | Brass/Pre-tin   | 175124-1 | —               | —        | —               | —                                    |
|                                                                                                                                    |                                        |                    | —               | —        | —               | —        | —               |                                      |
|                                                                                                                                    | 0.5~1.25mm <sup>2</sup><br>(AWG#20-16) | Ø1.2-2.2mm         | Brass/Pre-tin   | 175095-1 | —               | —        | —               | —                                    |
|                                                                                                                                    |                                        |                    | —               | —        | —               | —        | —               |                                      |
| For an extra-thin jacketed cable<br>Crimp Specifications:114-5134                                                                  |                                        |                    |                 |          |                 |          |                 |                                      |