



RoHS



K66X Series High Density Right Angle PCB Mount

K66X Series Dimensions

Pictured with Board Lock Option, Dimensions in mm



Shell Size	A	B	C	C1	D	E
In	±.015	±.005	±.010	±.010	±.005	±.005
mm	±0.38	±0.13	±0.25	±0.25	±0.13	±0.13
15 (E)	1.213 30.81	.984 24.99	.643 16.33	.666 16.92	.090 2.29	.010 0.25
26 (A)	1.541 39.14	1.312 33.32	.971 24.66	.994 25.25	.090 2.29	.020 0.51
44 (B)	2.088 53.04	1.852 47.04	1.511 38.38	1.534 38.96	.090 2.29	.020 0.51
62 (C)	2.729 69.32	2.500 63.50	2.159 54.84	2.182 55.42	.095 2.41	.023 0.58

C = Exterior of Female Shell (S) C1 = Interior of Male Shell (P)

Electrical Characteristics

Rated Current: 1.5A

Rated Voltage: 29Vac

D-SUBMINIATURE CONNECTORS

K66X Series

Documentation & Ordering Information

Kycon Part

Part Number Builder

Series	Shell Size	Contact Type	PC Board Mounting Option	Front Panel Mounting Option	Plating Option
--------	------------	--------------	--------------------------	-----------------------------	----------------

Series

K66X - High Density D-Subminiature Connector,
Right Angle PCB Termination, .350" Footprint

Shell Size-Contact Option

E - 15 Contacts

A - 26 Contacts

B - 44 Contacts

C - 62 Contacts

Contact Type

P - Pin Contact (Plug)


S - Socket Contact (Receptacle)

PC Board and Front Panel Mounting Option


N - (4-40)Riveted Threaded Insert

NJ - (4-40)Riveted Threaded Insert with 4-40 Hex.Jack Screws

N Option



J Option



Plating Option

Blank - Gold Flash

30 - 30µ" Gold

Contact Kycon for VESA and other options

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kycon:](#)

[K66XHT-E15P-N](#)