





NOTES:

MATERIAL

1. Insulator Material: PBT+30%G.F, (UL94V-0), Grey
2. Contact Material : Brass
3. Contact Plating : 1u" Au selective Over Ni

ELECTRICAL

- 1.Current Rating : 3.0 AMP
- 2.Withstand Voltage : 1000V AC/minute
- 3.Contact Resistance : 20mΩ max
- 4.Insulation Resistance: 1000MΩ min

ENVIRONMENTAL



- ⑦ 1.Operation Temperature: -40°C to +105°C
2.Packing : Tube
3.10P~18P with slot "M" without slot "N"
20P~64P with slot "M" and "N"

Ordering Information

AWH xxG-02x2-IDC

No. of Contacts : —
10,14,16,20,26,
30,34,40,50,60,64

Latch Type
0 -without latch
2 -with short latches
3 -with long latches



RoHS compliant
Unit: mm



Scale	Free	⑨	Add gap size 0.40mm	28.06.2018	Xavier		Date	Name	Customer-No.	
TOLERANCE		⑧	Modify the shape of insulator	05.06.2017	Winnie	Drawn	25.01.2006	Alex		
X.X	±0.40	⑦	Change the packing tray into tube	21.09.2015	Winnie	Approved	28.06.2018	Winnie	ASSMANN WSW-No. AWH xxG-02x2-IDC	
X.XX	±0.25									
X.XXX	±0.15	⑥	Add UL file no.	12.12.2013	Winnie					
ANGLE	±3°	⑤	Upddate	29.03.2013	Amy					Drawing-No.
		④	Correct drawing of short latch	05.05.2010	Dean				ASS 2231 CO	
DIM	TOL	Id.	Modification	Date	Name					Replace

