

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT — TE Connectivity

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	ECR-16-012200	13JUL2017	FL	SY

NOTES:

1

2

3

4

5

6

7

8

9

PARTS PACKAGED UNASSEMBLED

BULKPAC

FOR MOUNTING INSTRUCTIONS SEE 114-19039

SUITABLE FOR 30-26 AWG (0,25-0,40 mm DIA) WITH 1,0 MM DIA MAX INSULATION

SUITABLE FOR 26-24 AWG (0,40-0,50 mm DIA) WITH 1,0 MM DIA MAX INSULATION

MATERIAL:
CONTACT: PHOSPHORBRONZE
HOUSING: LIQUID CRYSTAL POLYMER
COVERS: GLASSFILLED POLYESTER (BLACK)

FINISH CONTACTS:
0,8µm AU over 1,3µm Ni IN CONTACT AREA
REMAINDER 2,0µm MAX. TIN OVER 1,3 µm Ni

MAXIMUM CABLE DIAMETER
WHEN NOT EXCEEDING COVER LID: 2,6 mm
OTHERWISE: 4,0 mm

3D DRAWING DOESN'T SHOW FULL DETAILS

COVER LID

HOUSING ASS'Y

COVER BASE

CABLE TIE

35,8

11,0

13,6

21,5

5,7

2,0

4x

2,0

AMP

26-24 AWG CABLE CONNECTOR KIT

30-26 AWG CABLE CONNECTOR KIT

DESCRIPTION

NOTES

PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN D. TRUREN 26-SEP-96

CHK K. KOCAKOGLU 26-SEP-96

APVD B. MOOIJ -

PRODUCT SPEC

APPLICATION SPEC

WEIGHT 0.000000

CUSTOMER DRAWING

TE Connectivity

Z-PACK 2mm HM KIT

10 POS. LF UNSHIELDED CABLE CONNECTOR

SIZE A3

CAGE CODE 00779

DRAWING NO C-352167

RESTRICTED TO

SCALE

SHEET 1 OF 1

REV D

REP-138 (1/15)

(REV.04-91)