


18.52	17.6	20.5	54796-0901	90
16.52	15.6	18.5	54796-0801	80
12.52	11.6	14.5	54796-0601	60
10.52	9.6	12.5	54796-0501	50
8.52	7.6	10.5	54796-0401	40
6.92	6.0	8.9	54796-0321	32
C	B	A	MATERIAL NO.	Ck+

MODEL NO.	54796-***
-----------	-----------

REVISED EC NO: J2007-1035 DRAWN:MABEI CHK:KATOYODA APPR:NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	MODEL NO. SD-54796-003	THIRD ANGLE PROJECTION
		10 UNDER	± 0.2	DRAWN BY S. A IHARA	DATE '00/05/30	TITLE 0.4 B/B CONN REC ASSY WITHOUT NAIL (HGT=1.5)			
		10 OVER 30 UNDER	± 0.25	CHECKED BY T. ITO	DATE '02/04/03				
		30 OVER	± 0.3	APPROVED BY TO. YAMAGUCHI	DATE '02/04/03	MOLEX INCORPORATED			
		ANGULAR ±3 °		MATERIAL NO.					
	REV	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



注記 NOTES:

1. 使用材料 MATERIAL
ハウジング: 液晶ポリマー ガラス充填 UL94V-0 (黒)
HOUSING: LIQUID CRYSTAL POLYMER (GLASS FILLED)
UL94V-0 (COLOR: BLACK)
ターミナル: リン青銅 (t=0.15)
TERMINAL: PHOSPHOR BRONZE (t=0.15)
2. メッキ仕様 PLATING
ターミナル TERMINAL
金メッキ 0.25マイクロメートル以上 (コンタクト部)
GOLD 0.25MICROMETER MINIMUM (CONTACT AREA)
金メッキ 0.4マイクロメートル以下 (テール部)
GOLD 0.4MICROMETER MAXIMUM (TAIL AREA)
下地メッキ: ニッケルメッキ 1.5マイクロメートル以上
UNDER PLATING: NICKEL 1.5MICROMETER MINIMUM
- △ (全極数/2) = 偶数の場合に適用。
APPLY FOR (CIRCUIT/2)=EVEN.
4. 嵌合相手: 55622-***I
MATE WITH: 55622-***I
5. テール平坦度は、0.08以下
TAIL COPLANARITY TO BE 0.08MAXIMUM


A					REVISED		EC NO: J2007-1035		REV	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---		MODEL NO. 54796-***I		THIRD ANGLE PROJECTION										
			DRAWN: NABEJ		2006/10/17						10 UNDER		± 0.2		DRAWN BY S. AIHARA		DATE '00/05/30			TITLE 0.4 B/B CONN REC ASSY WITHOUT NAIL (HGT=1.5)									
			CHKD: KTOYODA		2006/10/19						10 OVER 30 UNDER		± 0.25		CHECKED BY T. ITO		DATE '02/04/03												
			APPR: NUKITA		2006/10/23						30 OVER		± 0.3		APPROVED BY TO. YAMAGUCHI		DATE '02/04/03			MOLEX INCORPORATED									
											ANGULAR		± 3 °		MATERIAL NO.		DOCUMENT NO.					SHEET NO.							
													DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-54796-003			2 OF 2									
															SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
tb_frame_A3_J_ME_S Rev. E 2006/04/15										9		8		7		6		5		4		3		2		1		EN-02JA(021)	

10 9 8 7 6 5 4 3 2 1



F

F

引き出し方向
PULL OUT
DIRECTION



"F"




DETAIL "F"

NOTES

- 製品詳細寸法については図面 SD-54796-003 を参照下さい。
RE DETAILED DIMENSION, SEE SD-54796-003
- 梱包数量：3000個/リール
NUMBER OF CONNECTORS：3000PCS/REEL
- リードテープ長さ LEAD TAPE LENGTH
20PCS. MIN. トップテープ接着部 (空エンボス)
TOP TAPE BONDED PART. (EMPTY)
部品挿入部
COMPONENT
SUPPLIER
末端部
(空部)
TAIL PART
(EMPTY)
400 MIN. 40 MIN.
- 材料 (MATERIAL)
キャリアテープ (CARRIER TAPE)：ポリプロピレン (POLYPROPYLENE)
トップテープ (TOPTAPE)：PET, PE, PEF
リール (REEL)：ポリスチレン (P.S.) <リサイクル材を含む>
POLYSTYRENE (P.S.) <RECYCLE MATERIAL CONTAINED>


引き出し方向
PULL OUT
DIRECTION



MODEL NO. 54796-***8

REVISED	EC NO: J2007-1035	DRWN: NABEJ 2006/10/17	CHKD: KTOYODA 2006/10/19	APPR: NUKITA 2006/10/23	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC		THIRD ANGLE PROJECTION
						10 UNDER	± 0.2	DRAWN BY S. A IHARA	DATE '00/05/30	TITLE 0.4 B/B REC ASSY W/O NAIL (HGT=1.5) EMBSTP PKG			
						10 OVER 30 UNDER	± 0.25	CHECKED BY T. ITO	DATE '02/04/03				
						30 OVER	± 0.3	APPROVED BY TO. YAMAGUCHI	DATE '02/04/03				
						ANGULAR ±3 °		MATERIAL NO.					
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-54796-004		1 OF 3						
	REV			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

A



24mm幅キャリアテープ
24mm WIDTH CARRIER TAPE

24	29.4	25.4	14.7	54796-0608	60
			12.7	54796-0508	50
			10.7	54796-0408	40
			9.1	54796-0328	32
キャリアテープ幅 CARRIER TAPE WIDTH	C	B	(A)	MATERIAL NO.	極数 CK+

MODEL NO. 54796-***8

REVISED EC NO: J2007-1035 DRWN: NABEI CHKD: KTOYODA APPR: NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
		10 UNDER	±0.2	DRAWN BY S. AIHARA	DATE '00/05/30	TITLE 0.4 B/B REC ASSY W/O NAIL (HGT=1.5) EMBSTP PKG					
		10 OVER 30 UNDER	±0.25	CHECKED BY T. ITO	DATE '02/04/03						
		30 OVER	±0.3	APPROVED BY TO. YAMAGUCHI	DATE '02/04/03	MOLEX INCORPORATED					
		ANGULAR	±3 °	MATERIAL NO.							DOCUMENT NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-54796-004				2 OF 3	
		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

