




PLUG ASSY
#2330381-2

.053
.055

.053
.0545

SECTION A-A
CENTER CONTACT CRIMP

METHOD OF GAGING CRIMP DIMENSIONS

1. THE CRIMP DIMS APPLY ONLY
TO THE ABOVE COMBINATIONS

.214
.221 FERRULE CRIMP

CABLE RG-142A

FERRULE

SUPERSEDED BY IS 2340

2	21045-6	RING-RETAINING	7
1	300449	PIN-RETAINING	6
1	39364	SPRING	5
1	39366	COLLAR	4
2	38783	PIN-RETAINING	3
2	1-304197-0	PIN-RETAINING	2
6	21045-3	RING-RETAINING	1

REVISION RECORD	DR	CHK	DATE
A	REVISED	BKS	1/16/63
B	REVISED	CM	1/24/64
C	REVISED	CM	4/24/64
D	REVISED	BKS	8-3/63
E	REVISED	PL BIF	11-25/63
F1	SUPD BY IS-2340	BKS	7-28/63

DESCRIPTION	69331-1
-------------	---------

DR	2-27-63	AMP	2-27-63
CHK	2-27-63	AMP	2-27-63
DE	2-27-63	AMP	2-27-63
WIRE - RANGE - INSULATION	RG-142A	TYPE	BNC
TOLERANCE EXCEPT AS NOTED	± .015	SCALE	1-1
LOC	M	NO	B
REV	E1	REV	E1

For replacement of parts other than listed, Tool should be returned to our Factory to insure proper Certifying adjustment.

CUSTOMER COPY
REFERENCE ONLY

AMP
AMP INCORPORATED
HARRISBURG, PENNA.

HAND TOOL ASSEMBLY

PRINT DIST

DIMENSIONS IN INCHES. DO NOT SCALE PRINT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[69331-1](#)