



HEYCO

Heyco® Original Series-35 Liquid Tight Cordgrips Pigtail, PG Hubs



CABLE DIA. RANGE				PART NO.		DESCRIPTION	UL or ENEC	PART DIMENSIONS											
Minimum		Maximum		Black	Gray			A Clearance Hole Dia.		B Max. O.A. Length		C Thread Length		D Wrenching Nut Thk.		E Wrenching Nut Flat Size			
in.	mm.	in.	mm.					in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.		
.064	1,6	.210	5,3	3464	3465	FLEX RLTF 7													
.114	2,9	.250	6,4	3237	3238	FLEX LTF 7	UL	.492	12,5	2.44	62,0	.33	8,4	.20	5,1	.59	15,0		
.069	1,8	.187	4,7	3466	3467	FLEX RLTF 9													
.181	4,6	.312	7,9	3240	3241	FLEX LTF 9	UL	.599	15,2	2.77	70,4	.34	8,6	.20	5,1	.75	19,1		
.069	1,8	.250	6,6	3468	3469	FLEX RLTF 11													
.230	5,8	.395	10,0	3243	3244	FLEX LTF 11	UL	.733	18,6	3.44	87,4	.39	9,9	.20	5,1	.86	21,8		
.170	4,3	.450	11,4	3246	3247	FLEX LTF 13.5	UL	.804	20,4	3.88	98,6	.41	10,4	.20	5,1	.95	24,1		
.230	5,8	.546	13,9	3249	3250	FLEX LTF 16	UL	.886	22,5	4.36	110,7	.45	11,4	.23	5,8	1.05	26,7		
.250	6,4	.485	12,3	3478	3479	FLEX RLTF 21													
.450	11,4	.709	18,0	3245	3248	FLEX LTF 21	UL	1.115	28,3	5.03	127,8	.52	13,2	.23	5,8	1.30	33,0		

Standard colors black and gray.



- Flexible Pigtail™ extender prevents sharp bends and extends cable life.
- IP 68 rated.
- Widest range of approved cable diameters.
- For use in clearance or threaded holes.
- Acme threads on body prevent skipping and speed installation.
- PG hub threads are steel conduit threads per DIN 40430.
- All nylon construction with TPE sealing gland resists salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. (This feature is not assessed by UL.)
- Multiple sizes for flexible cord diameters ranging from .064" (1,6 mm) to .709" (18,0 mm).
- We recommend using the fitting with the smallest maximum diameter that will fit your application.
- **Unassembled Nylon Locknuts INCLUDED.**
- For Heyco Liquid Tight Threaded Plugs, see page 3-32.
- Consult Heyco for cordgrips molded in other colors.

Material
Certifications

- Nylon 6/6 w/TPE Sealing Gland
- UL Listed under Underwriters' Laboratories File E51579
 - Recognized under the Component Program of Underwriters' Laboratories File E51579
 - CSA Certified by Canadian Standards Association File 93876C
- 94V-2
Static -40°F (-40°C) to 239°F (115°C)
Dynamic -4°F (-20°C) to 212°F (100°C)
IP 68 (70 PSI, 5 BAR)

Flammability Rating
Temperature Rating

IP Rating

*Quick
Specs*

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heyco:](#)

[3240](#) [3544](#) [3545](#) [3547](#) [3548](#)