




AMP WIRE RANGE	E13288 Listed	LR7189 Certified
1/0 AWG SOLID OR STRANDED	1/0 AWG SOLID OR STRANDED	1/0 AWG SOLID OR STRANDED

1 TIN PL 0.00254[.000100] MIN THK
PER ASTM B-545.

50	LOOSE PIECE	1	COPPER ASTM B-152 1.78±0.08[.070±.003] ANNEALED	36916
QTY	PACKAGE TYPE	FINISH	MATERIAL	PART NO.
MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F] MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		
VOLTAGE RATING: N/A		TE Connectivity		
CIRCULAR MIL AREA: 42.4-60.6mm² [83,700-119,500] SOLID OR STRANDED		TERMINAL, RING TONGUE, SOLISTRAND, WIRE SIZE: 50.0mm2 [1/0] AWG		
DIMENSIONS: mm [INCHES]		SIZE CAGE CODE DRAWING NO RESTRICTED TO		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		A300779C-36916		
MATERIAL SEE TABLE		CUSTOMER DRAWING		
FINISH SEE TABLE		SCALE 2:1 SHEET 1 OF 1 REV J3		