

Product SKU:	C1360.18.90
Product Description:	Speaker Wire, UL Listed (Wires, Misc.) 120V max., No. of Conductors: 2, Gauge Size (AWG): 20, Conductor/Strands: 10/30, Jacket: Premium Grade PVC - Clear - 500 Ft. Spool
Product Category:	Electronics - Special Applications - Audio, Video, and Entertainment Cable - Speaker Wire - Clear

**Product Construction:**

Conductor:	• 24 thru 12 AWG fully-annealed 1 bare, 1 tin stranded copper per ASTM B-174
Insulation/Jacket:	• Premium grade PVC

Product Specification:

No. of Conductors:	• 2
Conductor Size (AWG):	• 20
Conductor/Strands:	• 10/30
Jacket Color:	• Clear
Nominal Insulation Thickness (in):	• 0.020
Nominal Insulation Thickness (mm):	• 0.51
Nominal Outside Diameter (in):	• 0.085 x 0.160
Nominal Outside Diameter (mm):	• 2.16 x 4.06
Standard Packaging:	• 500' Spool
Standard Package Quantity:	• 2
UPC #:	• 079407902965

Put-up:	• 500
SCC-14:	• 50079407902966
Cube:	• 527.022
Weight Per Unit of Measure:	• .01
ColorOption:	• Clear

Product Information:

Applications:	• Hi-fi and stereo speaker wire • Juke boxes • Lamps • Radios • Suggested voltage rating: 120 Volts • Not for in-wall use
Compliances:	• UL Wires Misc. (UL: 120V)
Packaging:	• 1000' (305 m) Spools • 500' (152 m) Spools • Other put-ups available- consult Customer Service

Technical Specifications

[Unit Conversion Factors](#)

[Cable Design Equations - Balanced Pair](#)

[Insulation and Jacket Properties](#)

[Temperature Conversion Chart](#)

[Decimal and Unit Conversion Factors](#)

[Cable Design Equations - Braid Shield](#)

[AWG Conductor Chart](#)

[Conduit Capacity Chart](#)

[Cable Design Equations - Coaxial Cable](#)

[Engineering Prefixes](#)

[Coax Connector Cross Reference](#)

[Glossary](#)



**CAROL
BRAND**