

Daten & Signal, Inline Socket, 6.3 mm, 3-pole, solder terminal, shielded



Description

- Solder terminal:
- Data and Signal transfer
- Data and Signal Connectors 3-pole, shielded, straight

References

Alternative: Housing insulated

Weblinks


[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#)

Technical Data


Diameter	6.3 mm
Number of Poles	3-pole
Ratings DC	2 A / 12 VDC
Ratings AC	2 A / 12 VAC
Dielectric Strength	1000VDC
Insulation Resistance	> 10000 MΩ @ 500VDC

Allowable Operation Temp.	-20 °C to 70 °C
Terminal	solder terminal
Housing	screened
Style	straight
Lifetime	10000 Insertions

Dimensions



Diagrams



All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number
Data and Signal Plug/ Sockets	6.3	3-pole	solder terminal	4803.3300

Most Popular.

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 100 Pcs

Mating Inlets/Plugs

Category / Description

Data and Signal Plug/Socket Overview complete



4803, Plug, solder terminal, screened, 6.3 mm, 3-pole, straight, , UK-Connector	4803.1300
4803, Plug, solder terminal, insulated, 6.3 mm, 3-pole, straight, , UK-Connector	4803.1310
4803, Plug, solder terminal, insulated, 6.3 mm, 3-pole, angled, , UK-Connector	4803.1320

Data and Signal Plug/Socket further types to 4803 UK-Stecker, D=6,5mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schurter:

4803.33