






General ordering data

Order No.	8607750000
Part designation	MOZ 230Vac / 24Vdc 0.1A
Version	Optocoupler, 3 V...48 V DC , 0.1 A , Tension clamp connection
EAN	4032248267675
Qty.	10 pc(s).

Approvals

Approvals institutes



Control side

Max. input frequency	3 Hz
Nominal auxiliary voltage	No

Control side

Power rating	1.7 VA
Rated control voltage	230 V AC $\pm 10\%$

General data

Ambient temperature (operational)	-25 °C...+50 °C
Storage temperature	-40 °C...+60 °C
Climate	40°C/93% rel. humidity, no condensation
Connection system	Tension clamp connection
DIN Rail compatibility	TS 35
Solid-state type	SSS relay 24 V / 24 V / 0.1 A DC

Insulation coordination (EN 50 178)

Clearance and creepage distances for control side ≥ 5.5 mm

- load side

Dielectric strength for control side - load side	2.5 kV
Overvoltage category	III
Pollution severity	2
Rated impulse voltage	4 kV
Rated voltage	300 V
Separation acc. to VDE 0106	No

Load side

Leakage current	≤ 1 mA
Nominal auxiliary voltage	No
Nominal switching current	0.1 A
Nominal switching voltage	3 V...48 V DC
Protective circuit	Integrated free-wheel diode
Short-circuit-proof	No
Status indicator	Green LED
Switch-off delay	> 10 ms
Switch-on delay	< 6.5 ms
Voltage drop at max. load	≤ 1 V

Dimensions

Clamping range, max.	2.5 mm ²
Clamping range, min.	0.5 mm ²
Clamping range, nom.	1.5 mm ²
Length	94 mm
Height	91
Width	6.1 mm

Classifications

ETIM 2.0	EC001504
ETIM 3.0	EC001504
eClass 4.1	27-27-09-00
eClass 5.0	27-27-09-90
eClass 5.1	27-27-09-90

Similar products

Order No.	Part designation	Version
8633020000	MOS 5Vdc / 24Vdc 0,1A	Optocoupler, 3... 48 V DC , 0.1 A , Screw connection
8633010000	MOZ 5Vdc / 24Vdc 0.1A	Optocoupler, 3... 48 V DC , 0.1 A , Tension clamp connection
8607340000	MOS 24Vdc / 24Vdc 0.1A	Optocoupler, 3 V... 48 V DC , 0.1 A , Screw connection
8607360000	MOZ 24Vdc / 24Vdc 0,1A	Optocoupler, 3 V... 48 V DC , 0.1 A , Tension clamp connection
8607690000	MOS 120Vuc / 24Vdc 0.1A	Optocoupler, 3 V... 48 V DC , 0.1 A , Screw connection
8607730000	MOZ 120Vuc / 24Vdc 0.1A	Optocoupler, 3 V... 48 V DC , 0.1 A , Tension clamp connection
8607710000	MOS 230Vac / 24Vdc 0.1A	Optocoupler, 3 V...48 V DC , 0.1 A , Screw connection
4061180000	SSS Relais 24V/24V 0,1Adc	Solid-state relay, 3...48 Vdc , 100 mA/ DC , Plug-in connection
4061230000	SSS Relais 60V/24V 0,1Adc	Solid-state relay, 3...48 Vdc , 100 mA/ DC , Plug-in connection