



Sample photo

Order symbol: AB 153410
Product nbr: 7083700
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074058867
El. number:
Finland: 3435484
Denmark: 8212003606

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		340	150	101	Ingress Protection (EN 60529): IP 66/67
inch:		13.4	5.9	4.0	Impact Resistance (EN 62262): IK 07
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Cover screws material:		Stainless steel			NEMA Class: NEMA 1, 4, 4X, 12, 13
Gasket material:		Polyurethane			Certificates:
Temperatures:					Gost R
Short term:		-40 ... 80 °C			
Continuous:		-40 ... 60 °C			
Short term:		-40 ... 175 °F			
Continuous:		-40 ... 140 °F			
Accessories:					
TM 1534		Mounting plate			
TRH 34		DIN-35 Mounting rail			
TRH 15		DIN-35 Mounting rail			
TF 28037		Wall fastening lug (4 pcs)			
TH A		Grey plastic hinges (2 pcs)			

