



THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.


Rating	16A 125VAC 10A 250VAC		
Contact Resistance		50m ohm Max.	
Insulation Resistance		DC 500V 100M ohm Min.	
Dielectric Strength		AC 2500V 1 minute	
Operation Temp.		- 25 ° C ~ 85 ° C	
Function		6P DPDT ON - ON	

Mounting Hole





Frame: Black, Nylon 66 (94-V2)
Actuator: Black, PC (94-V2)
Waterproof rubber: Black, Silicone
Terminals: Silver plated, Copper alloy
Printed: None
Waterproof: IP65



RoHS Compliant

2 Added date code. 1/28/11.

 INDUSTRIES Southampton, Pa. 18966 Tel 215.355.7080/www.cwind.com	Date Drawn: 1/28/11	Rev. 2	Unit: mm	Checked By: G.Guld
	Title: ROCKER SWITCH	CW P/N: GRB244C802BB		