

CONFIGURATION		PART NUMBER
Female Receptacle, 4 Pin, 3.6mm, Shell 16		RT00164SNH
DIMENSIONS		
Technical drawings of the RT360 connector showing dimensions and components. Labels: O-Ring, Insert, Shell, Seal Gasket, MASTER KEYWAY, UNEF 15/16-20 THREAD, PANEL CUT OUT REFERENCE. Dimensions: $\varnothing 23.60$, 26.9, 1.80, 11.30, 24.60, 31.0, 4-$\varnothing 3.20$, 24.60, 31.0, 24.60, 24.60, $\varnothing 24.60$ (For Front Panel Mounting), $\varnothing 28.10$ (For Rear Panel Mounting), 4-$\varnothing 3.30$.		
TECHNICAL DATA		
TEMPERATURE RANGE:	-40°C to + 105°C	
PROTECTION:	IP67 in mated condition and in combination with sealed backshell	
VOLTAGE RATING:	400v	
HOUSING BODY:	Zinc Alloy, Nickel Plated	
COUPLING NUT:		
INSERT:	Glass-filled Thermoplastic UL94-V0	
SEAL:	NBR	
CURRENT:	46A	
CONTACT SIZE:	3.6mm	
APPROVALS:	UL ECBT2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[RT00164SNH](#)