

YAEV25-L3

BURNDY® PRODUCTS

YAEV25-L3

YAEV25-L3 : 1/0 NYLON HVY DTY RING 1



ACTIVE

RoHS
compatible[Assistant](#)[Add to Favorites](#)[Email Datasheet](#) [Print Datasheet](#)

FCI Brings You More

[Contact our sales/technical support](#)[Sample request](#)[Price request](#)

Specifications

[Download document](#)

Dimensional	
Physical	
Approvals / Certifications	
Other Features	
Dimensional	
Strip length (Wire)	11/16 in.
Stud Hole (Size)	1/2 in.
Tongue Angle	Straight
Tongue Width (in)	0.88 in.
Wire Shroud	No
Insulation Diameter (Max)	0.564 in.
Physical	
Conductor Size	1/0 AWG
Conductor Type	Commercial/Military Stranded Copper
Insulation Type	Nylon
Color Code	Blue
Conductor Size (Range)	1/0 AWG
Approvals / Certifications	
Military Listed	MS15036-134
UL Listed	No
CSA Certified	No
Military Specification	Class 1
Other Features	
Tongue Type	Ring
Bulk Catalog Number	Same
UPC	78181002757
Keyword	smtermHD