

Part Number **BME.0M.200.XAZ**

Size/Series 0MN / M

[Request a quote](#)**MECHANICAL DETAILS**

Shell Style/Model BME*: Blanking caps for fixed receptacle (knurled grip)

Keying

Housing Material Environment friendly aluminium (nickel plated, anthracite color) shell and nut, other pieces bronze/brass

Cable Fixing Variant : 0 - 0 mm

PERFORMANCE DETAILS

Contact LEMO for performance details.

OTHER CHARACTERISTICS

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz]

Shock Resistance: 100 g [6 ms]

Operating temperature: -55°C/ +200°C

Climatical Category: 15/200/21 (Al. shell)

Lighting strike EIA 364-75 10K amps - 6 times

EMI Shielding EIA 364-66A -1Ghz-80 dB,3GHz-70 dB,6GHz- 58dB

IP Rating 50

Catalog

[Copyright](#) [Privacy policy](#) [Product safety](#)

