




2-To-1 Shrink Ratio 0-Halogen (Continued) One-Sided Printable B-7641 Wire Markers



Part Number	Markers Per Box	Range of Wire Diameter Inch (mm) Min.-Max.	Approx. Wire Gauge	Marker Width Inch (mm) A	Marker Height Inch (mm) B	Vert Repeat Inch (mm) C	Suggested Ribbon
1.500" Marker Width (Continued)							
2HSZ-187-150-WT	1,000	0.094 (2.4) - 0.151 (3.8)	14 to 10	1.496 (38.0)	0.343 (8.7)	1.000 (25.4)	R4307
2HSZ-187-150-YL	1,000	0.094 (2.4) - 0.151 (3.8)	14 to 10	1.496 (38.0)	0.343 (8.7)	1.000 (25.4)	R4307
2HSZ-187-150-**	1,000	0.094 (2.4) - 0.151 (3.8)	14 to 10	1.496 (38.0)	0.343 (8.7)	1.000 (25.4)	R4307
2HSZ-250-150-WT	1,000	0.125 (3.2) - 0.215 (5.5)	12 to 8	1.496 (38.0)	0.445 (11.3)	1.000 (25.4)	R4307
2HSZ-250-150-YL	1,000	0.125 (3.2) - 0.215 (5.5)	12 to 8	1.496 (38.0)	0.445 (11.3)	1.000 (25.4)	R4307
2HSZ-250-150-**	1,000	0.125 (3.2) - 0.215 (5.5)	12 to 8	1.496 (38.0)	0.445 (11.3)	1.000 (25.4)	R4307
2HSZ-375-150-WT	500	0.188 (4.8) - 0.320 (8.1)	8 to 4	1.496 (38.0)	0.445 (11.3)	2.000 (50.8)	R4307
2HSZ-375-150-YL	500	0.188 (4.8) - 0.320 (8.1)	8 to 4	1.496 (38.0)	0.626 (15.9)	2.000 (50.8)	R4307
2HSZ-375-150-**	500	0.188 (4.8) - 0.320 (8.1)	8 to 4	1.496 (38.0)	0.626 (15.9)	2.000 (50.8)	R4307
2HSZ-500-150-WT	500	0.250 (6.4) - 0.450 (11.4)	3 to 1	1.496 (38.0)	0.823 (20.9)	2.000 (50.8)	R4307
2HSZ-500-150-YL	500	0.250 (6.4) - 0.450 (11.4)	3 to 1	1.496 (38.0)	0.823 (20.9)	2.000 (50.8)	R4307
2HSZ-500-150-**	500	0.250 (6.4) - 0.450 (11.4)	3 to 1	1.496 (38.0)	0.823 (20.9)	2.000 (50.8)	R4307
2HSZ-750-150-WT	500	0.375 (9.5) - 0.700 (17.8)	2 to 250	1.496 (38.0)	1.236 (31.4)	2.000 (50.8)	R4307
2HSZ-750-150-YL	500	0.375 (9.5) - 0.700 (17.8)	2 to 250	1.496 (38.0)	1.236 (31.4)	2.000 (50.8)	R4307
2HSZ-750-150-**	500	0.375 (9.5) - 0.700 (17.8)	2 to 250	1.496 (38.0)	1.236 (31.4)	2.000 (50.8)	R4307
2HSZ-1000-150-WT	300	0.450 (11.4) - 0.950 (24.1)	1 to 500	1.496 (38.0)	1.634 (41.5)	2.500 (63.5)	R4307
2HSZ-1000-150-YL	300	0.450 (11.4) - 0.950 (24.1)	1 to 500	1.496 (38.0)	1.634 (41.5)	2.500 (63.5)	R4307
2HSZ-1000-150-**	300	0.450 (11.4) - 0.950 (24.1)	1 to 500	1.496 (38.0)	1.634 (41.5)	2.500 (63.5)	R4307
2HSZ-1500-150-WT	100	0.750 (19.0) - 1.40 (35.6)	-	1.496 (38.0)	2.433 (61.8)	2.500 (63.5)	R4307
2HSZ-1500-150-YL	100	0.750 (19.0) - 1.40 (35.6)	-	1.496 (38.0)	2.433 (61.8)	2.500 (63.5)	R4307
2HSZ-1500-150-**	100	0.750 (19.0) - 1.40 (35.6)	-	1.496 (38.0)	2.433 (61.8)	2.500 (63.5)	R4307
2HSZ-2000-150-WT	100	1.00 (25.4) - 1.90 (48.3)	-	1.496 (38.0)	3.165 (80.4)	2.500 (63.5)	R4307
2HSZ-2000-150-YL	100	1.00 (25.4) - 1.90 (48.3)	-	1.496 (38.0)	3.165 (80.4)	2.500 (63.5)	R4307
2HSZ-2000-150-**	100	1.00 (25.4) - 1.90 (48.3)	-	1.496 (38.0)	3.165 (80.4)	2.500 (63.5)	R4307
2.00" Marker Width							
2HSZ-094-2-WT	1,000	0.047 (1.2) - 0.080 (2.0)	18 to 16	1.969 (50.0)	0.197 (5.0)	1.000 (25.4)	R4307
2HSZ-094-2-YL	1,000	0.047 (1.2) - 0.080 (2.0)	18 to 16	1.969 (50.0)	0.197 (5.0)	1.000 (25.4)	R4307
2HSZ-094-2-**	1,000	0.047 (1.2) - 0.080 (2.0)	18 to 16	1.969 (50.0)	0.197 (5.0)	1.000 (25.4)	R4307
2HSZ-125-2-WT	1,000	0.062 (1.6) - 0.110 (2.8)	18 to 12	1.969 (50.0)	0.244 (6.2)	1.000 (25.4)	R4307
2HSZ-125-2-YL	1,000	0.062 (1.6) - 0.110 (2.8)	18 to 12	1.969 (50.0)	0.244 (6.2)	1.000 (25.4)	R4307
2HSZ-125-2-**	1,000	0.062 (1.6) - 0.110 (2.8)	18 to 12	1.969 (50.0)	0.244 (6.2)	1.000 (25.4)	R4307
2HSZ-187-2-WT	1,000	0.094 (2.4) - 0.151 (3.8)	14 to 10	1.969 (50.0)	0.343 (8.7)	1.000 (25.4)	R4307
2HSZ-187-2-YL	1,000	0.094 (2.4) - 0.151 (3.8)	14 to 10	1.969 (50.0)	0.343 (8.7)	1.000 (25.4)	R4307
2HSZ-187-2-**	1,000	0.094 (2.4) - 0.151 (3.8)	14 to 10	1.969 (50.0)	0.343 (8.7)	1.000 (25.4)	R4307
2HSZ-250-2-WT	1,000	0.125 (3.2) - 0.215 (5.5)	12 to 8	1.969 (50.0)	0.445 (11.3)	1.000 (25.4)	R4307
2HSZ-250-2-YL	1,000	0.125 (3.2) - 0.215 (5.5)	12 to 8	1.969 (50.0)	0.445 (11.3)	1.000 (25.4)	R4307
2HSZ-250-2-**	1,000	0.125 (3.2) - 0.215 (5.5)	12 to 8	1.969 (50.0)	0.445 (11.3)	1.000 (25.4)	R4307
2HSZ-375-2-WT	500	0.188 (4.8) - 0.320 (8.1)	8 to 4	1.969 (50.0)	0.445 (11.3)	2.000 (50.8)	R4307
2HSZ-375-2-YL	500	0.188 (4.8) - 0.320 (8.1)	8 to 4	1.969 (50.0)	0.626 (15.9)	2.000 (50.8)	R4307
2HSZ-375-2-**	500	0.188 (4.8) - 0.320 (8.1)	8 to 4	1.969 (50.0)	0.626 (15.9)	2.000 (50.8)	R4307

**** Note:** Other colors available for special order. Please contact our Brady Identification Solutions Distributor or Customer Service Representative for more information. When special ordering a colored sleeve, replace ** with the abbreviation of the desired color. Colors available for special order include: Black (BLK), Light Red (LR), Light Orange (LO), Light Blue (LB), Light Green (LGR), Light Gray (LGY), or Light Violet (LV).