



Main

Enclosure type	Weatherproof enclosure
Range of product	Kaedra
Device short name	Kaedra for modular devices
Accessories included with enclosure	2 terminal block 32 holes 2 terminal block supports 4 marking kits 4 wiring straps

Complementary

Enclosure mounting	Surface
Type of front cover	Reversible Transparent
Number of horizontal rows	4
Number of 18 mm modules per row	18
Total number of 18 mm modules	72
Type of rail	DIN
Number of pre-cutouts PG ISO	17
Number of terminal blocks	2 with 32 outgoers
Distribution block outgoers	32 x 10 mm ² 32 x 16 mm ²
Locking options description	Optional keylock
Enclosure material	Plastic
Width	448 mm
Height	842 mm
Depth	160 mm
Colour	Door : transparent green Enclosure : light grey (RAL 7035)

Environment

Standards	EN 50102 EN 50262 IEC 60439-3 IEC 60529 IEC 670
Fire resistance	750 °C
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK09 conforming to EN 50102
Electrical shock protection class	Class II
Ambient air temperature for operation	-25...60 °C
RoHS EUR conformity date	0648
RoHS EUR status	Compliant