

HSS Split Point Jobber Drills

Metric



DIN 338/BS 328

Flute Geometry

Standard Helix, right hand spiral

Surface finish

Blue

Point geometry

Up to 2.9mm - 118°

3.0mm and above - 135° split point

505492

Size (mm)	Flute Length (mm)	Overall Length (mm)	Order Code	Price Each
0.30	3	19	137-5882	
0.40	5	20	137-5883	
0.50	6	22	137-5884	
0.60	7	24	137-5885	
0.70	9	28	137-5886	
0.75	9	28	137-5887	
0.80	10	30	137-5888	
0.90	11	32	137-5889	
1.00	12	34	387-1034	
1.10	14	36	137-5711	
1.20	16	38	155-2166	
1.25	16	38	137-5995	
1.30	16	38	137-5715	
1.40	48	40	137-5717	
1.50	18	40	387-1046	
1.60	20	43	155-2167	
1.70	20	43	137-5723	
1.75	20	43	137-5890	
1.80	22	46	155-2337	
1.90	22	46	137-5727	
2.00	24	53	387-1058	
2.05	24	49	137-5892	
2.10	24	53	155-2169	
2.20	27	53	155-2171	
2.25	27	53	137-5893	
2.30	27	53	137-5732	
2.35	30	57	137-5894	
2.40	30	57	155-2252	
2.45	30	57	137-5895	
2.50	30	57	387-1060	
2.60	30	57	155-2172	
2.65	33	61	137-5896	
2.70	33	61	155-2173	
2.75	33	61	137-5897	
2.80	33	61	155-2174	
2.90	33	61	137-5743	
3.00	33	61	387-1071	
3.10	36	70	155-2175	
3.20	36	70	155-2176	
3.30	36	70	387-1290	
3.40	39	70	155-5803	
3.50	39	70	387-1083	
3.60	39	70	155-2576	
3.70	39	70	155-2339	
3.80	43	75	155-2577	
3.90	43	75	137-5754	
4.00	43	75	387-1095	
4.10	43	75	155-2341	
4.20	43	75	387-1307	
4.30	47	80	155-2578	
4.40	47	80	137-5759	
4.50	47	80	387-1101	
4.60	47	80	137-5761	
4.70	47	80	137-5762	
4.80	52	86	155-2342	
4.90	52	86	22-3767	
5.00	52	86	387-1113	
5.10	52	86	155-2343	
5.20	52	86	155-2344	
5.30	52	86	137-5769	
5.40	57	93	147-7446	
5.50	57	93	387-1125	
5.60	57	93	22-3772	
5.70	57	93	137-5772	
5.80	57	93	137-5773	
5.90	57	93	137-5774	
6.00	57	93	387-1137	
6.10	63	101	137-5777	
6.20	63	101	155-5804	
6.30	63	101	137-5779	
6.40	63	101	22-3779	
6.50	63	101	387-1149	
6.60	63	101	137-5782	
6.70	63	101	147-7447	
6.80	69	109	387-1319	
6.90	69	109	137-5784	
7.00	69	109	387-1150	
7.10	69	109	147-7448	
7.20	69	109	155-2998	
7.30	69	109	147-7449	
7.40	69	109	147-7450	
7.50	69	109	155-5701	
7.60	75	117	147-7451	
7.70	75	117	147-7452	
7.80	75	117	147-7453	

7.70	75	117	147-7452
7.80	75	117	147-7453
7.90	75	117	147-7454
8.00	75	117	387-1174
8.10	75	117	155-5702
8.20	75	117	155-2481
8.30	75	117	147-7455
8.40	75	117	147-7457
8.50	75	117	387-1186
8.60	81	125	147-7458
8.70	81	125	147-7459
8.80	81	125	155-5703
8.90	81	125	147-7460
9.00	81	125	387-1198
9.10	81	125	02-5043
9.20	81	125	147-7461
9.30	81	125	147-7462
9.40	81	125	147-7463
9.50	81	125	387-1204
9.60	87	133	147-7464
9.70	87	133	147-7465
9.80	87	133	147-7466
9.90	87	133	147-7467
10.00	87	133	387-1216
10.10	87	133	02-5107
10.20	87	133	387-1435
10.30	87	133	02-5109
10.40	87	133	02-5110
10.50	87	133	387-1228
10.60	87	133	02-5111
10.70	94	142	02-5112
10.80	94	142	02-5113
10.90	94	142	02-5114
11.00	94	142	387-1230
11.10	94	142	148-5472
11.20	94	142	148-8975
11.30	94	142	148-5473
11.40	94	142	148-5474
11.50	94	142	387-1241
11.60	94	142	148-5475
11.70	94	142	148-5476
11.80	94	142	148-5478
11.90	101	151	148-5479
12.00	101	151	387-1253
12.10	101	151	148-5480
12.20	101	151	148-8976
12.30	101	151	148-8977
12.40	101	151	148-5481
12.50	101	151	387-1265
12.60	101	151	148-5482
12.70	101	151	02-5255
12.80	101	151	148-5483
12.90	101	151	148-5484
13.00	101	151	387-1277
13.10	101	151	147-7469
13.20	101	151	147-7471
13.30	108	160	147-7472
13.40	108	160	147-7473
13.50	108	160	147-7474
13.60	108	160	02-5266
13.70	108	160	02-5296
13.80	108	160	02-5268
13.90	108	160	02-5270
14.00	108	160	02-5271
14.50	114	169	148-5485
15.00	114	169	147-7475
15.50	120	178	148-5486
16.00	120	178	148-5487
16.50	125	184	148-5488
17.00	125	184	148-5491
17.50	130	191	148-8978
18.00	130	191	02-5291
18.50	135	198	148-5492
19.00	135	198	148-5494
19.50	140	205	02-5294
20.00	140	205	148-5493