






DESCRIPTION: RJ-45 TO 15-POSITION MALE D-SUB – PLASTIC & METALIZED PLASTIC

MATERIAL:
HOOD: ABS UL 94V-HB



RJADK15P70808Y1

SERIES _____
POSITIONS _____
15
GENDER _____
P = MALE
D-SUB TERMINALS _____
7 = CRIMP & POKE (CONTACTS PRE-CRIMPED)
MODULAR POSITIONS _____
08
MODULAR POSITIONS LOADED _____
08
COLOR _____
1 = BLACK
2 = METALIZED (SHIELD RATING: 60dB)
3 = GRAY
D-SUB CONTACT PLATING _____
1 = GOLD FLASH

RJ45

1. BLUE
2. ORANGE
3. BLACK
4. RED
5. GREEN
6. YELLOW
7. BROWN
8. WHITE

DB-15M

1 2 3 4 5 6 7 8

9 10 11 12 13 14 15

FRONT VIEW

DO NOT SCALE FROM DRAWING

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 05-15-07		
		CHECKED:		DATE:		
NorComp			SCALE: N.T.S.	SHEET 1	OF 1	REV 1
			DWG NO. RJADK15P70808Y1			