

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020163](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway Rubber Hand Lamp with 300W, Open End Vinyl Coated Guard, with Receptacle, 15.24m (50.0') 16/3 SOOW-A

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130102](#)
NEMA Configuration NEMA 5-15
Outlet Side
Overview [Hand Lamps](#)
Product Name Super-Safeway
Type Hand Lamps
UPC 78678860544

Physical

Cord Length - Primary 15.24m (50.0')
Cord Length - Secondary N/A
Depth 190.50mm (7.500")
Duty Industrial
Guard Included Yes
Guard Type Insulated, Open End
Height 371.35mm (14.620")
Length N/A
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A23
Lamp Wattage - Maximum 300W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 240V

Material Info

Engineering Number 111UIB163



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130102](#) Series