




PAN-TY LOOPS FOR
CABLE HOLD-DOWNS
(4 PLACES)

POST FOR TAMPER
RESISTANT SCREW



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [] ARE IN METRIC.
4. BOX INCLUDES:
 - 1- BOX BASE
 - 1- BOX COVER
 - 4- PLT1.51-M PAN-TY
 - 1- LABEL/ LABEL COVER
 - 2- MOUNTING SCREW
 - 1- MOUNTING SCREW (USED TO SECURE COVER TO BASE)
 - 2- STRIP OF 3.00" X .75" FOAM TAPE FOR MOUNTING
5. BASE HAS FOUR POCKETS FOR OPTIONAL MAGNET (CBM-X)
6. BREAKOUTS DESIGNED TO ACCEPT LD5/LDP5 AND LD5/LDP10 RACEWAY.
7. BASE MATERIAL THICKNESS= .090[2.29].

DRAWING FILENAME		MO2479EX_DC130_00A.PRT		SIZE A	
MINI-COM 12 POSITION SURFACE MOUNT BOX CUSTOMER DRAWING					
 PANDUIT ™ CORP. TINLEY PARK, ILL 60477		1.1. NUMBER N/A			
		PRODUCT SPEC N/A			
 THIRD ANGLE PROJECTION		WORK INSTRUCTION N/A			
		SCALE NONE			
DRAWN BY JsP		MATERIAL: BOX: ABS		PART NO. CBX12♦♦-AY	
DATE 12-27-06				DRAWING NO. 02479-130	
CHK'D 					