

Miniature Fuse, 10.3 x 38 mm, Super-Time-Lag TT, 250 VAC



NF C 93-435 · 250 VAC · Super-Time-Lag TT



NNO

Description

- Low Breaking Capacity

Standards

- NF C 93-435 - Modell HA29

References

This type is Phase-out without alternate type
Last order date: 31.12.2012


Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Rated Voltage	125 - 250 VAC
Rated current	1.6 - 50 A
Breaking Capacity	300 A - 500 A
Characteristic	Super-Time-Lag TT
Mounting	Fuseholder / Clip
Admissible Ambient Air Temp.	-40 °C to 55 °C
Climatic Category	40/055/56 acc. to IEC 60068-1
Material: Terminals	Nickel-Plated Copper Alloy
Material: Tube	Glass
Material: Endcaps	Nickel-Plated Copper
Unit Weight	9 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	HA29, Rated current, Characteristic


Dimension



Pre-Arcing Time

Rated Current In	1.1 x In min.	1.45 x In max.	3.0 x In min.	3.0 x In max.	5.0 x In min.	5.0 x In max.
1.6 A - 6.3 A	60 min	60 min	4 s	9 s	500 ms	4 s
8 A - 50 A	60 min	60 min	4 s	20 s	2 s	6 s

Time-Current-Curves



All Variants

Rated Current [A]	Rated Voltage [VAC]	Breaking Capacity	Voltage Drop 1.0 In typ. [mV]	NNO		Order Number
0.2	250	1)	1700	●		7037.1110
0.31	250	1)	650	●		7037.1120
0.4	250	1)	840	●		7037.1130
0.5	250	1)	680	●		7037.1140
0.63	250	1)	490	●		7037.1150
1	250	1)	365	●		7037.1170
1.25	250	1)	310	●		7037.1210
1.6	250	1)	620	●		7047.1110
2.5	250	1)	430	●		7047.1220
3.15	250	1)	295	●		7047.1230
4	250	1)	250	●		7047.1240
5	250	1)	200	●		7047.1250
6.3	250	1)	190	●		7047.1260
8	250	1)	200	●		7047.1270
10	250	1)	160	●		7047.1280
12.5	250	1)	160	●		7047.1290
15	250	1)	110	●		7047.1310
20	250	1)	95	●		7047.1330
25	250	1)	80	●		7047.1340
30	125	1)	75	●		7047.1350
40	125	-	50	●		7047.1410
45	125	-	55	●		7047.1420
50	125	-	45	●		7047.1430

Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 300 A @ 50 VAC , p.f. ≥ 0.9 / 500 A @ 125 VAC , p.f. = 0.7 - 0.8

Packaging Unit Small Box Pack (10 pcs.)