




- 1 CONTINUOUS STRIP ON REELS.
- 2 FEED IS 16.51 ± 0.076 [$.650 \pm .005$].
- 3 ACCEPTS WIRE SIZE [#20-#16] AWG.
- 4 INSULATION RANGE TO BE 2.29-3.30
[.090-.130] DIA.
- 5 MATING TAB THK TO BE 0.813 ± 0.025
[.032 $\pm$.001].



VIEW A-A
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	
DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±- 1 PLC ±- 2 PLC ±0.25 [0.010] 3 PLC ±- 4 PLC ±- ANGLES ±-
MATERIAL H04 BRASS	FINISH SEE TABLE