







Rating	20A 12V DC	Mounting Hole	Circuit Diagram
Contact Resistance	50M ohm Max		
Insulation Resistance	DC 500V 100M ohm Min		
Dielectric Strength	AC 1500V 1 Minute		
Switch Function	3P SPST ON-OFF		

Descriptions:
Switch: R13-61L2, 3P SPST ON-OFF
toggle switch.
Panel: ABS, Black.
Protection Rack: Nickel plated metal.



sw1 sw2 sw3



Notices: Could be used for most of SCI toggle switches.
and the toggle length better less than 25mm.
±0.5mm Unless otherwise specified.

02/10/'10	歐陽安	1.依客戶要求改為不附螺絲.2.未標示尺寸公差±0.3-→±0.5				△
Date	Name	Descriptions				△
Drawn	Checked	Approved	SCI BOM No.	1130332	Model Name	Panel Switch
歐陽安	楊金2		Customer No.		Model No.	PR18-R3A-61L2-N
02/09/'10	02/09/10'		Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.	REV. X1