

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19202-0027

Status:

Active

Overview:

[Splice](#)

Description:

Funnel Entry Butt Splice for 14-16 AWG Wire

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-19902-011 \(PDF\)](#)

[Product Specification PS-19902-013 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL

E32244

General

Product Family

Splices

Series

19202

Crimp Quality Equipment

Yes

Mil-Spec

N/A

Overview

[Splice](#)

Product Name

Butt - Funnel Entry

UPC

800753047723

Physical

Barrel Type

Closed

Flammability

94V-2

Insulation

Nylon (PA)

Net Weight

1.351/g

Packaging Type

Adhesive Tape on Reel

Wire Insulation Diameter

4.70mm max. Funnel End, 5.05mm max.

Wire Size AWG

14, 16

Material Info

Old Part Number

BS-942-DK

Reference - Drawing Numbers

Product Specification

PS-19902-011, PS-19902-013

Sales Drawing

SD-19202-001



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19202Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade™	0640010100
Hand Crimp Tool	
Hand Crimp Tool	0640010300
Crimp Head for the	0640050300
AT-200™ Pneumatic	
Hand Tool	
Crimp Head for the	0640050100
AT-200™ Pneumatic	
Hand Tool	