






ASSEMBLY - VIEW FROM FRONT




6' FOOT TWIST
POWER CORD
(NEMA L5-20P)


ASSEMBLY - VIEW FROM BOTTOM



SECTION A-A



ISOMETRIC VIEW



ASSEMBLY - VIEW FROM SIDE

1589H8C1BKRF

Finish - Front - Black Painted Steel

Back - Black Painted Steel

Rated - 125 VAC, 60 Hz, 20 Amps

Approvals - CSA Certified Standards C22.2 (No. 21-95, 42-99)

- UL Recognized Standard UL1363

Cord Length

1589H8C1BKRF - 6' Foot Twist Power Cord (NEMA L5-20P)

1589H8D1BKRF - 15' Foot Twist Power Cord (NEMA L5-20P)



**HAMMOND
MANUFACTURING™**

1589H8C1BKRF

www.hammondmfg.com