

Dome Plugs



This nylon dome plug is ideal for covering unwanted openings, with its convex, matt finished head tapering to a thin edge for an excellent appearance. As the dome plugs are manufactured from nylon 6,6 they offer a good resistance to most solvents, aromatic hydrocarbons, dilute alkalis, detergents, oils, greases, and fats. They also offer a limited resistance to dilute acids and offer a short term working temperature

DURATOOL

New

between -40 and 100°C.

The dome plug is quick and easy to install. Fingertip pressure will lock the dome plug firmly into panels to provide a neat finish. The plug head height is only 1.6mm.

UL/CSA Description	Mounting Hole Diameter (mm)	Max. Chassis Thickness (mm)	Plug Head Diameter (mm)	Overall Height (mm)
DP-187	4.8	1.6	6.4	5.9
DP-250	6.4	1.6	7.9	7.9
DP-312	8.0	1.6	9.5	7.9
DP-375	9.5	3.2	11.9	10.3
DP-437	11.0	3.2	13.5	10.3
DP-500	12.7	3.2	14.7	10.3
DP-562	14.3	3.2	16.7	10.3
DP-625	15.9	3.2	18.2	10.3
MDP-16	16.0	2.5	18.5	10.3
DP-687	17.5	3.2	19.8	10.3
DP-750	19.0	3.2	23.4	10.3
MDP-20	20.0	2.5	22.6	10.3
DP-812	20.6	3.2	22.6	10.3
DP-875	22.2	3.2	25.8	11.5
MDP-25	25.0	2.5	29.8	11.5
DP-1000	25.4	3.2	30.6	11.5
DP-1093	27.8 - 28.6	3.2	30.9	11.5

492107

UL/CSA Description	Pack Qty	Order Code	Price Per Pack
DP-187	25	151-4449	
DP-250	25	151-4450	
DP-312	25	151-4451	
DP-375	25	151-4452	
DP-437	25	151-4454	
DP-500	25	151-4455	
DP-562	25	151-4456	
DP-625	25	151-4457	
MDP-16	25	151-4458	
DP-687	25	151-4459	
DP-750	25	151-4460	
MDP-20	25	151-4461	
DP-812	25	151-4462	
DP-875	25	151-4463	
MDP-25	25	151-4464	
DP-1000	25	151-4466	
DP-1093	25	151-4467	