



Solderless Stackup Banana Plug

Wire firmly held in place with internal setscrew, eliminating soldering. Assembly of test leads simplified. **Upper:** Banana jack — 4.22 mm (0.166) dia. brass. **Lower:** Banana plug spring — One piece heat treated beryllium copper. Fits standard 4.22 mm (0.166) dia. banana jack. **Rating:** 5000 WVDC, 15 amps, +50°C (+122°F) max. +150°C (+302°F).

885-0301, 1325-0, Black		PER PKG./10	12.50
885-0302, 1325-2, Red		PER PKG./10	12.50
885-1327, 1325-4, Yellow		PER PKG./10	12.50
885-0305, 1325-5, Green		PER PKG./10	12.50

Features integral safety collar that insulates exposed wire leads. Wire firmly held in place with internal setscrew, eliminates soldering, simplifies assembly of test leads. **Upper:** Banana jack — 4.22 mm (0.166) dia., brass. **Lower:** Banana plug, spring — One piece heat treated beryllium copper. Fits standard 4.22 mm (0.166) dia. banana jack. **Rating:** 5000 WVDC, 15 amps, +50°C (+122°F) max.

885-0460.	1825-0. Black.	PER PKG./10	12.50
885-0462.	1825-2. Red.	PER PKG./10	12.50
885-1827.	1825-3. Orange.	PER PKG./10	12.50
885-0464.	1825-4. Yellow.	PER PKG./10	12.50
885-0465.	1825-5. Green.	PER PKG./10	12.63
885-1830.	1825-6. Blue.	PER PKG./10	12.50
885-0469.	1825-9. White.	PER PKG./10	12.50

Material: Banana plug body — Brass; Spring — One piece heat treated beryllium copper. Fits standard 4.22 mm (0.166) dia. banana jack. **Finish:** Nickel plated. **Rating:** 5000 WVDC, 15 amps.

Furnished with hex nut and tin plated solder lug.
885-3263. 3263. 6.32 x 12.7 (0.50) ThreadPER PKG./10 13.50

Mounts to various size panels. Furnished with screw and tin plated solder lug.

885-3265.	3265. 6.32 × 6.4 (0.25) Screw	PER PKG./10	16.00
885-3266.	3266. 8.32 × 6.4 (0.25) Screw	PER PKG./10	16.00

Setscrews secure leads. Simplifies cable construction or component mounting. Double banana jack — 4.22 mm (0.166) dia., brass. Double banana plug, spring — One piece heat treated beryllium copper. Fits standard 4.22 mm (0.166) dia. banana jack. **Rating:** 5000 WVDC, 15 amps, 50°C (-122°F) max.

885-2970. 2970-0. Black	EACH	4.30
885-2971. 2970-2. Red	EACH	4.30

Double banana jack — 4.22 mm (0.166) dia., brass, nickel-plated. Double banana plug, spring — One piece heat treated beryllium copper, nickel plated. Fits standard 4.22 mm (0.166) dia. banana jack.

Terminals — Fig. C
MDP-ST standard double banana plug with solder turrets.
Rating: 5000 WVDC, 15 amps, +55°C. Similar to Model
MDP, except has bright tin plated solder turret terminals
for permanent noise-free connections of cables and
components. Black Polypropylene insulation.
885-0021. MDP-ST. EACH 3.00

Setscrews secure leads. Features recess for mounting small components. ABS Insulation.

885-1330. 1330-0. Black	EACH	2.35
885-1331. 1330-2. Red	EACH	2.35

Fig. E
Banana plug internally shorted with #18 AWG wire.
Banana jacks provide top stackup. Cross holes 4.22 mm
(0.166) dia. in body provide side stackup connections.
ABS Insulation.

885-0110. MDP-S-0. Black.....	EACH	3.50
885-0023. MDP-S-2. Red.....	EACH	3.50
885-0024. MDP-S-9. White.....	EACH	3.50

¹/₂" diameter hole with included hex nut and washer. ST designates solder terminals; the other terminals are available. Tins plastic. Nickel and gold also available. Insulation: Nylon. Rating: 100V.

885-6020	.6387-ST-1-0 Black	PER PKG./10	\$5.00
885-6021	.6387-ST-1-1 Brown	PER PKG./10	\$5.00
885-6019	.6387-ST-2 Red	PER PKG./10	\$5.00
885-6030	.6387-ST-3 Yellow	PER PKG./10	\$5.00
885-6031	.6387-ST-4 Orange	PER PKG./10	\$5.00
885-6032	.6387-ST-5 Green	PER PKG./10	\$5.00
885-6033	.6387-ST-6 Blue	PER PKG./10	\$5.00
885-6037	.6387-ST-7 Violet	PER PKG./10	\$5.00
885-6039	.6387-ST-8 Gray	PER PKG./10	\$5.00
885-6042	.6387-ST-9 White	PER PKG./10	\$5.00

Mounts in panels from 1.60 mm (0.063) to 9.53 mm (0.375) thick. Nickel plated lockwasher and 1/4-32 hex nut. **Material:** Brass. **Rating:** 2500 WVDC, 15 amps, +115°C (+239°F) max.

885-0400.	1581-0. Black	PER PKG./10	9.00
885-0401.	1581-2. Red	PER PKG./10	9.00
885-1583.	1581-4. Yellow	PER PKG./10	9.00
885-1584.	1581-5. Green	PER PKG./10	9.09
885-1585.	1581-6. Blue	PER PKG./10	9.00
885-1586.	1581-9. White	PER PKG./10	9.00

885-2854.	2854-0. Black	PER PKG./10	18.50
885-2855.	2854-2. Red	PER PKG./10	18.50
885-2856.	2854-4. Yellow	PER PKG./10	18.50
885-2857.	2854-5. Green	PER PKG./10	18.50
885-2859.	2854-6. Blue	PER PKG./10	18.50
885-2860.	2854-9. White	PER PKG./10	18.50

Threaded for rapid mounting. Used with standard banana plugs. Furnished with hex nut and solder lug. **Material:** Banana jack and hex nut — Brass; Solder lug — copper. **Finish:** Banana jack and hex nut — Nickel plated; Solder lug — Tin plated. **Rating:** 15 amps.

885-3267. 3267. Unassembled.....PER PKG./10 8.50

Accepts standard banana plug. Thin line design not for high-density packaging. Nickel plated 0.002-0.02 inch nut and lockwashers included. 2.54 mm (0.100) in. pitch. Lead is perpendicular with flat on insulator. Mounts in panels 1.57 mm (0.62) to 6.35 mm (0.250) thick. **Rating:** 3500 WDCV, 15 amps, +115°C (+239°F) max. **Finish:** 3760 Tin plated; 3770 — Gold plated; 3770 — Gold plated with titanium cure.

885-3760, 3760-0, Black,	EACH	2.45
885-3761, 3760-2, Red,	EACH	2.45
885-3762, 3760-5, Green,	EACH	2.45
885-3760, 3750-0, Black,	EACH	3.60
885-3765, 3750-2, Red,	EACH	3.60
885-3760, 3770-0, Black,	EACH	5.00
885-3762, 3770-2, Red,	EACH	5.00

Max
20-32
(1.31)
0.85
(0.033)
0.002
(0.05)
0.002
(0.05)
F

Material: Binding post body, nuts, lockwasher — Gold plated. Meets MIL-P-55149/1A. **Rating:** 1500 VRMS, 30 amps, +80°C (+176°F) max.

885-5018. 5018-0. Black.....	EACH	7.90
885-5019. 5018-2. Red.....	EACH	7.90

Accepts miniature banana plug. #8-32 hex nut and lockwasher included. 2.2 (0.086) dia. cross hole is perpendicular with center of mounting hole. Max. hole depth to 4.8 (0.188) thick. **Material:** Binding post body, captive thumb nut and hex nut — Brass; Lockwasher — Steel. **Finish:** Binding post with one captive thumb nut — Gold (2382) or bright tin plated (2439); Hex nut and lockwasher — Nickel plated (2439). **Mounting:** 10mm. **Rating:** 1500 VDC, 5 amps, +115°C (+239°F) max.

885-2382, 2382-2, Black,	EACH	3.85
885-2383, 2383-2, Red,	EACH	3.85
885-2439, 2439-0, Black,	EACH	2.90
885-2440, 2439-2, Red,	EACH	2.90

Nickel-plated 8-32 hex nut and lockwasher included. One red and one black tin plated binding post (type 3760) with double mounting base. **Material:** Double binding post with captive thumb nut — Brass. Accepts standard banana plug. **Finish:** Bright tin plated. **Insulation:** Polycarbonate. **Rating:** 2500 WVDC, 15 amps, +115°C (+239°F) max.

885-4243. 4243-0. Black, unassembled	EACH	4.85
885-4244. 4243-2. Red, unassembled	EACH	4.85

Meets MIL-P-55149/8.	
885-4995. 4995-0. Black	EACH 13.70
885-4997. 4995-2. Red	EACH 13.70

Insulated binding post for rapid mounting of components and test leads. End accepts standard banana plug, cross-hole accepts test probe tips or lead wires up to 0.10" diameter. Center cross-hole accepts standard banana plugs. Insulation: Polycarbonate, ABS. Rating: 2500 VDC, 15, A. 50°C (122°F).

885-6013. 2894-0 Black	EACH	4.15
885-6014. 2894-2 Red	EACH	4.15



Mounts in panels from 1.60 mm (0.063) to 9.53 mm (0.375) thick. Nickel plated lockwashers and 1/4-32 hex nut. One black and one red jack. Choice of black or red mounting base. **Material:** Brass. **Finish:** Bright tin plated. **Rating:** 2500 WVDC, 15 amps +115°C (+239°F) max. Jacks are spaced at 0.75 inch centers.

885-2269.	2269-0. Black	EACH	2.50
885-2270.	2269-2. Red	EACH	2.50

Permits single banana plug to be used with equipment having barrier strips. Lugs fit a no. 8 or 10 screw. Banana jack — 4.2 (0.166) dia., brass, nickel plated. **Insulation:** ABS. 0.8 (0.03) thick spade lug. Copper, electro-tin plated. **Rating:** 5000 VDC, 15 amps, +50°C (+122°F) max.

885-3779.	3777A-0. Black.....	EACH	1.25	
885-3781.	3777A-2. Red.....	EACH	1.33	

Provides rapid method for splicing single banana plug patch cords. Reduces the necessity of storing extra long patch cords. Molded thermoplastic body provides protective insulation. 4.22 mm (0.166) dia. banana jack. **Material:** Brass. **Finish:** Nickel plated. **Insulation:** Polypropylene. **Rating:** 5000 WDC, 15 amps, +55°C. (+131°F) max.

885-1829. 1829-0. Black.....PER PKG./10 14.00

Figure 1 shows the dimensions of the test specimens. The dimensions are as follows:

- Specimen K:**
 - Top diameter: 4.79 (122) Dia
 - Top diameter: 4.06 (103) Dia
 - Length: 3.95 (102)
 - Bottom diameter: 2.29 (58) Dia
 - Bottom diameter: 2.67 (68) Dia
 - Bottom diameter: 7.62 (200)
- Specimen L:**
 - Top diameter: 7.87 (201) Dia
 - Length: 2.15 (55) L.D. (0.95)
 - Length: 28.19 (711)
 - Bottom diameter: 7.62 (200)
- Specimen M:**
 - Top diameter: 4.83 (123) Dia
 - Length: 11.19 (284)
 - Bottom diameter: 7.62 (200)
- Specimen N:**
 - Top diameter: 2x4 (10) Dia
 - Top diameter: 4.65 (118) Dia
 - Length: 2.29 (58)
 - Bottom diameter: 7.62 (200)
 - Bottom diameter: 3x
- Specimen O:**
 - Top diameter: 3.8 (97) Dia
 - Length: 4.40 (112) Thd
 - Length: 2.29 (58)
 - Bottom diameter: 3.66 (93) Max

Excellent for riveting to panels or boards. Solder turret for rapid attachment of wires. Mount in 1.57 mm (0.062) panel. **Material:** Miniature banana plug body — Brass; Spring — One piece heat treated beryllium copper. Fits miniature 2.64 mm (0.104) dia. banana jack. **Finish:** Gold plated. **Rating:** 2500 WVDC, 5 amps. **885-3273. 3273..... PER PKG./10 10.00**

Wire firmly held in place with setscrew. The integral collar insulates leads and acts as a strain relief by preventing the flexing of lead at setscrew. **Upper:** Miniature banana jack — 2.64 mm (0.104) dia., brass, gold plated. **Insulation:** ABS. **Lower:** Miniature banana plug, spring — One piece heat treated beryllium copper, gold plated. Fits miniature 2.64 mm (0.104) dia. banana jack. **Rating:** 2500 WDC, 5 amps, +50°C (+122°F) max.

885-2945. 2945-0. Black	EACH	3.00
885-2946. 2945-2. Red	EACH	3.00

Miniature in-line plug for use with miniature binding posts or banana jacks. Wire is soldered directly to threaded plug. **Material:** Miniature banana plug body — Brass; Spring — One piece heat treated beryllium copper. Fits miniature 2.64 mm (0.104) dia. banana jack. **Finish:** Gold plated. **Insulation:** Nylon. **Rating:** 2500 WVDC, 5 amps, +80°C (+176°F) max.

885-3690.	3690-0. Black; Dim. "L" = 11.43 (0.45)	PER PKG./10	16.50
885-3691.	3690-2. Red; Dim. "L" = 11.43 (0.45)	PER PKG./10	16.50

Excellent for riveting to panels or boards. **Material:** Miniature banana plug body — Brass; Spring — One piece heat treated beryllium copper. Fits miniature 2.64 mm (0.104) dia. banana jack. **Finish:** Gold plated. **Rating:** 2500 WVDC, 5 amps.

885-3268. 3268. Dim. "X" = 2.39 (0.094)	PER PKG./10	10.00
885-3272. 3272. Dim. "X" = 3.96 (0.156)	PER PKG./10	10.00

Threaded stud for rapid mounting. Solder turret for attachment of wires. Furnished with nickel plated 4-40 hex nut, unassembled. **Material:** Miniature banana plug/body — Brass; Spring — One piece heat treated beryllium copper. Fits miniature 2.6 (0.104) dia. banana jack. **Finish:** Gold plated. **Rating:** 2500 VDC, 5 amps.

885-3276.	3276.	Dim. "X" = 8.8 (0.230).	Unassembled	PER PKG./10	11.50
885-4513.	4513.	Dim. "X" = 12.2 (0.480).	Unassembled	PER PKG./10	16.50