

Thermal Transfer Raised Panel Labels



- Raised thermal transfer printable surface with high-tack adhesive for strong holding power
- Variety of sizes and colors for a wide range of applications
- Thermal transfer print technology provides crisp, clear, and durable text
- Use with Panduit thermal transfer resin ribbons

Part Number	Part Description	Width		Height		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm		
C100X050APT	White, raised panel component label.	1.00	25.4	0.50	12.7	500	2000
C100X050AOT	Black, raised panel component label.	1.00	25.4	0.50	12.7	500	2000
C200X100APT	White, raised panel component label.	2.00	50.8	1.00	25.4	500	2000
C200X100AOT	Black, raised panel component label.	2.00	50.8	1.00	25.4	500	2000
C300X100APT	White, raised panel component label.	3.00	76.2	1.00	25.4	500	2000
C300X100AOT	Black, raised panel component label.	3.00	76.2	1.00	25.4	500	2000
C400X100APT	White, raised panel component label.	4.00	101.6	1.00	25.4	500	2000
C400X100AOT	Black, raised panel component label.	4.00	101.6	1.00	25.4	500	2000
C252X030APT	White, raised panel component label.	2.52	64.0	0.30	7.6	500	2000
C252X030AOT	Black, raised panel component label.	2.52	64.0	0.30	7.6	500	2000
C379X030APT	White, raised panel component label.	3.79	96.3	0.30	7.6	500	2000
C379X030AOT	Black, raised panel component label.	3.79	96.3	0.30	7.6	500	2000

Ultimate ID® Network System Laser/Ink Jet Labels



- Ultimate ID® Network Labeling Software is included at no charge with each package of laser/ink jet labels
- Labels can be printed in both laser and ink jet printers
- Designed to efficiently support TIA/EIA-606-A standard labeling requirements
- Laser and ink jet labels for use with Ultimate ID™ Faceplates, Patch Panels, Marker Ties, Modular Furniture Faceplate, and Surface Mount Boxes
- Durable multi-layer construction
- Non-adhesive labels are easily removed from 8.5" x 11" label sheets
- Unique non-adhesive material configuration
- Ultimate ID™ Labels are part of a complete system for identification designed to efficiently support TIA/EIA-606-A standard labeling requirements



Part Number†	Part Description	Width		Height		Std. Pkg. Qty.	Std. Ctn. Qty.
		In.	mm	In.	mm		
UILJ1	White, non-adhesive polyester labels, 264 per sheet, 1-port labels.	0.68	17.3	0.24	6.0	5	50
UILJ2	White, non-adhesive polyester labels, 132 per sheet, 2-port labels.	1.32	33.4	0.24	6.0	5	50
UILJ3	White, non-adhesive polyester labels, 99 per sheet, 3-port labels.	1.95	49.5	0.24	6.0	5	50
UILJ4	White, non-adhesive polyester labels, 66 per sheet, 4-port labels.	2.59	65.7	0.24	6.0	5	50
UILJ6	White, non-adhesive polyester labels, 66 per sheet, 6-port labels.	3.86	97.9	0.24	6.0	5	50
UILJCOMBO	White, non-adhesive polyester labels, combination sheet with forty 1-port, sixty 2-port, three 3-port and twenty-four 4-port labels.	—	—	0.24	6.0	5	50

For Electrical Ivory labels, add EI to end of part number.
Order number of sheets required in multiples of Std. Pkg. Qty.