









Rating	16A 125VAC, 10A 250VAC, T85 °C 	Mounting Hole 
	10(4)A 250VAC, 25T85 	
Contact Resistance	50m ohm Max.	
Insulation Resistance	DC 500V 100M ohm Min.	
Dielectric Strength	AC 1500V 1 minute	
Operation Temperature	-25°C~85°C	
Switch Function	4P DPST ON-OFF(Illuminated)	





Frame: Black, Nylon 66
Actuator: Blue, PC
Printed: White, hot stamping

Circuit Diagram



C8\R13\R13-244B-02(1824356)

								△
								△
Date	Name	Description						NO
Drawn	Checked	Approved	SCI BOM NO.	1824356	Model Name	ROCKER SWITCH		
曹 盈 芳			Customer No.		Model No.	R13-244B-02	REV.	0
11/18/'08	11/18/'08	11/18/'08	Unit	mm	 SHIN CHIN INDUSTRIAL CO., LTD.			