



NOTES:

- 1 MAXIMUM RECOMMENDED STROKE: .500.
- 2 FOR USE WITH 206-375 TOOL, FOR OTHER TOOLS AND/OR STROKE COMBINATIONS, REFER TO STROKE LIMITER CHART (HK1122) OR CONSULT AN AFS/HUCK SALES SPECIALIST.
- 3 SHIP WITH: STOP 126747 AND DEFLECTOR 126748-1.
- 4 128624C ASSEMBLY CONSISTS OF 128514C COLLET AND 128488 DRAWBAR.
- 5 127132C ASSEMBLY CONSISTS OF 127078C ANVIL HOLDER AND 120308 ANVIL INSERT.

REV	DESCRIPTION	DET	DATE
D	ITEM 3, 130052 WAS 128071	EL	11/11/11
E	128514C WS 128624C. ADDED 128488	JJC	07/31/12

(E) 128488	1	DRAWBAR	9
126748-1	1	UNITIZED DEFLECTOR	8
(E) 128514C	1	COLLET	7
126745	1	GUARD	6
120095	1	DEFLECTOR	5
122912	1	BARBED RETAINER	4
130052	1	UNITIZED CHUCK JAW	3
127582	1	TOP GUARD	2
127132C	1	ANVIL ASSEMBLY	1
PART NO.	QTY	DESCRIPTION	ITEM

IDENTIFICATION PER SPEC 42-311: ★ ETCH	HUCK INTERNATIONAL, INC., I.S.D 1 CORPORATE DR KINGSTON, NEW YORK 12401		
ITAR/ECCN: EAR99	CLEARANCE NOSE ASSEMBLY -08 LONG ASP		
SCH B#: 8467.99.0190	FINAL ASSY: -		
HTS: 8467.99.0190	ENG: MVM CK: B	DATE: 10/13/04	SCALE: 2:1
		99-3729-1C	