


Technical drawing of a mechanical part with dimensions:

- Overall width: 1.26 [32.0]
- Overall height: 1.00 [25.4]
- Internal width (from left face to start of taper): 0.63 [16.0]
- Internal height (from bottom face to start of taper): 0.63 [16.0]




FULL SCALE

| PANDUIT<br>PART<br>NUMBER* | MAXIMUM<br>CABLE DIA.<br>in. (mm) | WEIGHT<br>lbs. (g)/100pcs |
|----------------------------|-----------------------------------|---------------------------|
| LWC50-A                    | 0.50<br>(12.7)                    | 0.84<br>(379)             |

\*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION, FOR PACKAGE SIZE.

- 2) MOUNT IS DESIGNED TO SUPPORT  
0.63 lbs [284g] MAX WEIGHT ON  
A CLEAN DRY SMOOTH SURFACE.



ADHESIVE BACKING: PRESSURE SENSITIVE FOAM  
0.04 [1.0] THICK WITH PROTECTIVE LINER TO  
EXTEND BEYOND EDGE FORMING A TEAR TAB.

DIMENSIONS IN BRACKETS ARE METRIC [ mm ]

GB0161BA\_PB\_LWC50A\_02

# PANDUIT

CORP.

TINLEY PARK, ILLINOIS

LWC50-A, LATCHING WIRE CLIP

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X)  $\pm 0.05$  (1.3) (.XXX)  $\pm 0.010$  (0.25)  
(.XX)  $\pm 0.02$  (0.5) ANGLES  $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

|                                   |
|-----------------------------------|
| <p><b>DRAWN BY</b> <u>JRI</u></p> |
|-----------------------------------|

MAT'L:

|      |         |
|------|---------|
| DATE | 11-5-93 |
|------|---------|

NYLON 6/6

|       |    |
|-------|----|
| SCALE | 2X |
|-------|----|

2X

DRAWING NO.

GB0161BA

DWG  
A  
SIZE

|     |          |      |     |                                      |          |      |     |  |  |  |
|-----|----------|------|-----|--------------------------------------|----------|------|-----|--|--|--|
|     |          |      |     |                                      |          |      |     |  |  |  |
|     |          |      |     |                                      |          |      |     |  |  |  |
|     |          |      |     |                                      |          |      |     |  |  |  |
|     |          |      |     |                                      |          |      |     |  |  |  |
| 2   | 11-10-00 | CGSM |     | CORRECTED 0.67 DIMENSION PLACEMENT   | GB0161BA | 2    |     |  |  |  |
| 1   | 1-7-98   | CGSM |     | CHANGED NOTE 3 ON APPLICATION INSTR. | GB0161BA | 1    |     |  |  |  |
| R   | 11-5-93  | JRL  |     | INITIAL RELEASE                      | GB0161BA | R    |     |  |  |  |
| REV | DATE     | BY   | CHK | DESCRIPTION                          | ECN - R  | CUST | SUP |  |  |  |