




FEATURES:

- Spade lug attaches securely to a screw terminal while the medium size alligator test clip can quickly grab onto terminal points.
- Spade lug and alligator bodies are nickel plating for tarnish resistance
- The alligator features a flex boot for insulation protection.
- Alligators clip has .187" (4.75mm) max. jaw opening.

MATERIALS:

Alligator: Body: Steel, Nickel Plated

Spring: Stainless Steel

Flex Boot: Vinyl

Wire: 18 AWG, Stranding: 65 X 36 tinned copper, PVC Insulation, .144" (3.66 mm) O.D.

Marking: "POMONA 1960-XX"

Spade Lug: Body: Brass, Nickel Plated

Insulation: Polypropylene molded to the spade lug and wire. Color matches wire.

RATINGS:

Operating Voltage: 150 VRMS

Current: 5 Amperes

Operating Temperature: +50°C (+122°F)

ORDERING INFORMATION: Model 1960-XX-*

XX = Length in inches

Standard Lengths: 36" (91.44cm),

- = Color of Flex Boot and Wire, -0 Black, -2 Red
- Additional lengths and colors can be quoted upon request.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA