


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT<br>PART NUMBER | STUD<br>SIZE | DIMENSIONS in.    |                   |                   |                   |                   |
|------------------------|--------------|-------------------|-------------------|-------------------|-------------------|-------------------|
|                        |              | A <sup>±.03</sup> | W <sup>±.01</sup> | C <sup>±.02</sup> | M <sup>±.03</sup> | H <sup>±.01</sup> |
| PV6-8RX                | #8           | 1.61<br>(40.89)   | .47<br>(11.94)    | .43<br>(10.92)    | 1.37<br>(34.8)    | .17<br>(4.32)     |
| PV6-10RX               | #10          | 1.61<br>(40.89)   | .47<br>(11.94)    | .43<br>(10.92)    | 1.37<br>(34.8)    | .20<br>(5.08)     |
| PV6-14RX               | 1/4"         | 1.61<br>(40.89)   | .47<br>(11.94)    | .43<br>(10.92)    | 1.37<br>(34.8)    | .27<br>(6.86)     |
| PV6-56RX               | 5/16"        | 1.73<br>(43.94)   | .62<br>(15.75)    | .51<br>(12.95)    | 1.42<br>(36.07)   | .33<br>(8.38)     |
| PV6-38RX               | 3/8"         | 1.73<br>(43.94)   | .62<br>(15.75)    | .53<br>(13.46)    | 1.42<br>(36.07)   | .39<br>(9.91)     |
| PV6-12RX               | 1/2"         | 1.83<br>(46.48)   | .82<br>(20.83)    | .53<br>(13.46)    | 1.42<br>(36.07)   | .52<br>(13.21)    |

**NOTES:**

1. UL LISTED FOR:
  - A. 600V MAX VOLTAGE RATING
  - B. 221° F (105° C) MAX TEMP RATING
  - C. #6 AWG STRANDED COPPER WIRE
2. PACKAGE QTY:   STD. PKG. -E=20  
                      BULK PKG. -T=200
3. MATERIAL:
  - A. STAMPING - .045" (1.14) THK COPPER,  
                  TIN PLATED
  - B. HOUSING - VINYL, BLUE
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. INSTALLATION TOOL:   CT-720
6. WIRE STRIP LENGTH: 7/16 <sup>+1/32</sup> <sub>-.0</sub> (11.1 <sup>+0.8</sup> <sub>-.0</sub>)



A41222\_04

|     |      |     |     |                                    |       |     |    |  <b>PANDUIT</b> CORP.      TINLEY PARK, ILLINOIS |       |       |             |
|-----|------|-----|-----|------------------------------------|-------|-----|----|---------------------------------------------------------------------------------------------------------------------------------------|-------|-------|-------------|
| 04  | 1/01 | KMD |     | CAD FILE SPEC. WAS N41222AA_PCD_03 |       |     |    | #6 BARREL VINYL INSULATED RING TONGUE<br>.436 (11.07) MAX. WIRE INSUL. DIAMETER                                                       |       |       |             |
| 03  | 4-95 | MS  |     | UPDATED NOTES AND DIMENSIONS       | 03206 |     |    |                                                                                                                                       |       |       |             |
| 02  | 7-88 | DW  |     | REDRAWN WITH REVISIONS             |       |     |    |                                                                                                                                       |       |       |             |
| REV | DATE | BY  | CHK | DESCRIPTION                        | ECN # | APP | PM | DRAWN BY                                                                                                                              | CHK'D | SCALE | DRAWING NO. |
|     |      |     |     |                                    |       |     |    | DAW                                                                                                                                   |       | NONE  | A41222      |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PV6-10RX-T](#) [PV6-38RX-T](#) [PV6-10RX-X](#) [PV6-38RX-X](#) [PV6-8RX-E](#) [PV6-8RX-T](#)