




MARKETING SALES DRAWING

DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



Notes:

- Tusonix Standard part number: 4101-001.
Tusonix RoHS compliant part number: 4101-001 LF.
Customer must specify Standard or RoHS part number when ordering.
- Lead finish: Standard Part No.: 60/40 solder plated. RoHS Part No. Silver Plated.
Eyelet finish Standard Part No.: 60/40 solder plated. RoHS Part No. Silver Plated.
- Part Marking: Standard has no marking. RoHS part: Green Dot.

MIN. CAP (pF)		WORKING VOLTAGE (WVDC)		CURRENT Idc	DWV @ 2 SEC.	I.R. MIN.	MINIMUM NO-LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220			
		85°C	125°C				10 MHz	100 MHz	1 GHz	10 GHz
1500		350	200	10A	700 VDC	10 G Ω	3	45	70	70

REVISION RECORD	Original Release C.O.	0	CAP. CHART 3 WAS 5 EC 12-17-91	8	RDRWN TO CMP. FRMT MTRC DMS ADDED. EC 8-19-96	9	REVISED I.L. TITLE. S.M. 01-16-97	10	REMOVED -S FROM TITLE & ADDED NEW FORMAT. S.M. 01-16-97	11	NOTES 1-3 & DWV ,IR , GREEN DOT ADDED L.E. 04-11-05	12	20050407-5-03	--TOLERANCES-- Unless Otherwise Specified		Title EYELET STYLE EMI FILTER	
												DECIMAL ±		.031 [.79]	Drawn E.C. 08-09-96		
												ANGLES ±					
												TUSONIX TUCSON, ARIZONA		Approved B.M. 08-09-96			
														A	4101-001		