


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOMINAL DUCT SIZES (W)	C REF	HC	TC
25	24.6 [.97]	8.9 [.35]	1.55 [.06]
37.5	37.1 [1.46]	"	"
50	49.6 [1.95]	"	"
62.5	62.1 [2.44]	"	"
75	74.6 [2.94]	9.4 [.37]	1.65 [.065]
100	99.6 [3.92]	"	"

NOTES:

- NOTES:
1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES
TO INDICATE COLOR AND OR PACKAGING QUANTITY.
2. ALL DIMENSIONS ARE IN MILLIMETERS [INCHES].

PART NO. SYSTEM
 COVER EXAMPLE 
 C 50 LG 2
 TYPE ———
 WIDTH (mm) ———
 COLOR ———
 LENGTH (M) ———

B A

CAD FILENAME/LAYERS

D34287_PVC_MET_COV_01A.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

EUROPEAN/METRIC WIRING DUCT COVER
FOR DUCT TYPE "AC", "BC", AND "MC"
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) :	(.XXX) :
(.XX) :	ANGLES :

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

MAT'L:

**POLYVINYL
CHLORIDE**

	SCALE
--	--------------

NONE

DRAWING NO.
34287-07

DWG
A
SIZE

--		----	---	C. ADDED PART NO. SYSTEM EXAMPLE	-----	---	---		
I	8-24-01	JCST	JKG	B. DUAL DIMENSIONED A. ADDED "AC" AND "BC" TO TITLE	34287-07	JKG	JKG		
R	12-20-93	DW	CEF	RELEASED TO PRODUCTION	34287-07	CEF	CEF		
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP	