

PANDUIT

1.13
(28.7)

PANDUIT

1.13
(28.7)

COUNT FOR

- COUNTERSUNK HOLE
FOR OPTIONAL #6 (M3)
SCREW OR 1/8" RIVET.

PANDUIT PART NUMBER*	WEIGHT lbs/100 pcs (g)/100 pcs	USE WITH THESE CABLE TIE CROSS-SECTIONS
ABMS-A	0.42 (189)	M, I, S

ADHESIVE BACKING:
PRESSURE SENSITIVE FOAM TAPE
0.04 (1.0) THICK WITH PROTECTIVE
LINER. MOUNT IS DESIGNED TO
SUPPORT 0.6 lb. (272g.) MAX. WEIGHT
ON A CLEAN, DRY, SMOOTH, GREASE-FREE
SURFACE.

NOTES:

- *1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATIONS FOR PACKAGE SIZE.
- 2) MOUNTS PROVIDED IN STRIPS OF TWO FOR EASY REMOVAL OF PROTECTIVE LINER.
- 3) MOUNTS WILL BE ORIENTED IN LINE WITH, OR 90° FROM EACH OTHER AS ILLUSTRATED ABOVE.

I	2/7/05	JAD	N/A	.205 WAS .200 CORRECTION: .17 WAS .250	GB0239GE	I				
R	2-11-99	CBSM		INITIAL RELEASE	GB0239GE	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			

C/O FILENAME LAYERS

G00239GE_DC_ABMS_01

PANDUIT

CORP. TINLEY PARK, ILLINOIS

ABMS-A
ADHESIVE BACKED MOUNT

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± 0.05 (.3) (.XXX) ± 0.010 (0.25)
(.XX) ± 0.02 (0.5) ANGLES $\pm 5^\circ$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

CCSM

MAT'L 2

SCALE

NONE

DATE _____

2-11-88

NYLON 6/6

EXPANDED 1993 1994

GB0239GE

Spice

A
817