



## Corrosion Resistant Slide Collection

*Presenting a full range of corrosion-resistant slide choices for installations where exposure to moisture or high humidity is a key environmental factor. These four stainless steel products are a great solution for drawers or pull-out shelves in:*

- outdoor kitchens
- poolside structures
- greenhouses
- garages
- sheds and barns
- marine cabinetry

...and more



**Accuride®**  
*Always Moving Forward*

# Corrosion Resistant Slide Collection

## Model SS2028

With the narrowest side space of the group, this model provides an advantage in installations where space must be maximized.


- 100-pound load rating\*
- 3/4 extension
- .38" cross section width
- Hold-in detent
- Non-disconnect
- 12"-28" in 2" increments†



## Model SS0330

Providing a load capacity on the lighter side of the heavy-duty category, this slide is for heavier drawers or pull-out shelves in applications that require full extension.



- 143-pound load rating\*
- Full extension
- .75" cross section width
- Hold-in detent
- Non-disconnect
- 12"-24" (2" increments), plus 28"†



## Model SS5322

The unique features on this model are over travel for complete access to contents, and bracket mounting, which provides a disconnect method.


- 265-pound load rating\*
- Full extension plus over travel
- .81" cross section width
- Hold-in detent
- 12"-24" (2" increments), 28" and 31"†
- Easy-mount brackets with locator pins to simplify disconnect. L-shaped brackets are placed over the pins and held in place by a snap ring on the front pin.



## Model SS5321

The most heavy-duty performer of the group, this slide offers a slightly narrower profile, over travel, and the greatest load rating of the collection.

- 350-pound load rating\*
- Full extension plus over travel
- .75" cross section width
- Hold-in detent
- Non-disconnect
- 12"-24" (2" increments), 28" and 31"†



**Note:** For applications with indirect exposure to humidity, consider Model CH3832, a regular steel slide with a special finish that provides 8 times more protection than a standard zinc finish.



\* Load rating based on 18" slides in an 18" wide drawer cycled 80,000 times.

† The lengths indicated in inches are approximate conversions from the metric measurements. Please see technical sheet for exact dimensions.

Authorized Distributor

**Accuride**

12311 Shoemaker Avenue  
Santa Fe Springs, CA 90670  
(562) 903-0200 • (562) 903-0208 Fax  
[www.accuride.com](http://www.accuride.com)