



BURNDY Catalog Number
UPC Number
Description
Status

YSM8C
7818108057944
8 AWG PARALLEL SPLICE
Active

Web Use
BURNDY Product Line

Dimensional

Strip Length 1/2
Length (in) 0.41

General

Product Description

Copper Compression Parallel
Splice, 6088-16864 Circular Mil,
0.41" Splice Length, Short Barrel,
Tin Plated

Conductor(s)

Copper Solid Size (Range) N/A
Copper Stranded (Range) 12 AWG-8 AWG

Physical

Type of Plating Tin
Plated (Yes or No) Y

Approvals / Certifications

UL Listed N
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175