

Cable marker - WMTB (24X8)R - 0816278

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable marker, Roll, white, Unlabeled, Can be labeled with: Thermomark R, Thermomark X, Thermomark S, Mounting type: Assembly with cable binders, Cable diameter: ≥ 6 mm, Lettering field: 24 mm x 8 mm

The figure shows the WMTB (35x15)R version

Why buy this product

- ☒ Made from high-quality polyester foil
- ☒ Labeling service: Phoenix Contact can custom-label all conductor markers according to your requirements
- ☒ The marker has two fastening eyes so that it can be attached to the conductor by means of PKB ... cable binders
- ☒ The marker has two fastening eyes so that it can be attached to the conductor by means of PKB ... cable binders

Key commercial data

Packing unit	1
Minimum order quantity	1
Catalog page	Page 175 (CL2-2011)
GTIN	 4 046356 125734
Weight per Piece (excluding packing)	731.0 GRM
Country of origin	GERMANY

Technical data

General

Length (b)	23 mm
Width (a)	17 mm
Color	white
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 120 °C
Components	free from silicone and halogen
Material	Polyester
Number of individual labels	4000
Number of individual labels per row	4

Cable marker - WMTB (24X8)R - 0816278

Classifications

eclass

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27149103
eCl@ss 6.0	27141137

etim

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

unspsc

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black