

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [73137-5013](#)
Status: **Active**
Overview: [BNC Miniature RF Connectors](#)
Description: BNC 50 Ohm, Right-Angle PCB Bulkhead Jack Receptacle, White PBT Housing, Height 13.20mm, Nut and Lockwasher included, Tin Plated Leads

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E107635

General

Product Family	RF/Coax Connectors
Series	73137
Comments	13.20mm Profile
Overview	BNC Miniature RF Connectors
Product Name	BNC
Style	PCB
UPC	800753692060
Wire/Cable Type	N/A

Physical

Cable Attachment	N/A
Flammability	94V-0
Gender	Jack
Keying to Mating Part	None
Net Weight	14.735/g
Orientation	Right Angle
PCB Mounting	Through Hole
PCB Thickness - Recommended	4.00mm
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Bulkhead

Electrical

Impedance	50#
-----------	-----


Solder Process Data

Duration at Max. Process Temperature (seconds)	10
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-73137-5013
---------------	---------------



EU RoHS

RoHS Compliant RF Product

REACH SVHC

Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[73137Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[73137-5013](#)