

Order Code

MHRJ - 45 - 8P8C - R - 30

Series
Type
RJ-22, RJ-11, RJ-12, RJ-45, RJ-48
Size and Contacts
4P4C (RJ22), 6P4C (RJ11), 6P6C (RJ12),
6P6C-OST (RJ12), 8P8C (RJ45),
10P10C (RJ48)
Cable Style
F = Flat or Oval, R = Round
Plating Options
Omit = 50u"
6 = 6u", 15 = 15u", 30 = 30u"



Order Code

RJ45SRB - QR - R

Strain Relief Boot
Omit = Bubble Boot (Anti Snag)
QR = Quick Release
Colour
LG = Grey, BK = Black, R = Red,
G = Green, BL = Blue, Y = Yellow

- Compatible with all FCC specifications
- 50µ" gold plated contacts as standard, but also available in 6, 15 and 30u" plating

- UL94V-0 polycarbonate body
- True knife blade, inusulating piercing contacts
- Compatible with standard crimping tools

Four Conductor/Four Position Handset Cord Plug Flat Cable Entry



Dimensions in mm

Four Conductor/Six Position Line Cord Plug Round Cable Entry



Dimensions in mm

Six Conductor/Six Position Line Cord Plug Round Cable Entry



Dimensions in mm

Eight Conductor/Eight Position Patch Cable Plug Round Cable Entry



Ten Conductor/ Ten Position

Dimensions in mm

McKEE HAGBORG CONNECTORS LTD, DARWIN ROAD, CORBY, NORTHANTS, NN17 5XZ.. ENGLAND
Tel:- (44) 01536 200963 Fax:- (44) 01536 201963 Website:- http://www.mhconnectors.com E.mail:- info@mhconnectors.com