


- All the data listed in this catalogue are for reference only,TAI-TECH reserves the right to alter or revise the specifications without prior notification.

■ FCI 3225 Series

Part Number	Thickness C size (mm)	Inductance (uH)	Q min.	Test Frequency (MHz)	SRF (MHz) min.	DC Resistance (Ohm) max.	Rated Current (mA)
FCI3225-R12□	1.3±0.2	0.12	30	25.2	500	0.22	450
FCI3225-R15□	1.3±0.2	0.15	30	25.2	450	0.25	450
FCI3225-R18□	1.3±0.2	0.18	30	25.2	380	0.28	420
FCI3225-R22□	1.3±0.2	0.22	30	25.2	350	0.32	420
FCI3225-R27□	1.3±0.2	0.27	30	25.2	260	0.36	420
FCI3225-R33□	1.3±0.2	0.33	30	25.2	220	0.40	400
FCI3225-R39□	1.3±0.2	0.39	30	25.2	200	0.45	400
FCI3225-R47□	1.3±0.2	0.47	30	25.2	180	0.50	370
FCI3225-R56□	1.3±0.2	0.56	30	25.2	150	0.55	320
FCI3225-R68□	1.3±0.2	0.68	30	25.2	140	0.60	300
FCI3225-R82□	1.3±0.2	0.82	30	25.2	130	0.65	280
FCI3225-1R0□	1.3±0.2	1.0	30	7.96	120	0.70	200
FCI3225-1R2□	1.3±0.2	1.2	30	7.96	100	0.75	150
FCI3225-1R5□	1.3±0.2	1.5	30	7.96	85	0.85	150
FCI3225-1R8□	1.3±0.2	1.8	30	7.96	80	0.90	150
FCI3225-2R2□	1.3±0.2	2.2	30	7.96	75	1.00	150
FCI3225-2R7□	1.3±0.2	2.7	30	7.96	70	1.10	120
FCI3225-3R3□	1.3±0.2	3.3	30	7.96	60	1.20	120
FCI3225-3R9□	1.3±0.2	3.9	30	7.96	55	1.30	120
FCI3225-4R7□	1.3±0.2	4.7	30	7.96	50	1.50	120
FCI3225-5R6□	1.3±0.2	5.6	30	7.96	47	1.60	120
FCI3225-6R8□	1.3±0.2	6.8	30	7.96	43	1.80	100
FCI3225-8R2□	1.3±0.2	8.2	30	7.96	40	2.00	90
FCI3225-100□	1.3±0.2	10.0	30	2.52	36	2.10	45
FCI3225-120□	1.3±0.2	12.0	30	2.52	33	2.50	45
FCI3225-150□	1.3±0.2	15.0	30	2.52	30	2.80	35
FCI3225-180□	1.3±0.2	18.0	30	2.52	27	3.30	35
FCI3225-220□	1.3±0.2	22.0	30	2.52	25	3.70	35
FCI3225-270□	1.3±0.2	27.0	30	2.52	20	5.00	15
FCI3225-330□	1.3±0.2	33.0	30	2.52	17	5.60	15

NOTE: □ :TOLERANCE J: +/-5% K: +/-10% L: +/-15% M: +/-20%.

■ Q-Frequency Characteristics



■ Inductance-Current Characteristics

