



Sample photo

Order symbol: PC 050504
Product nbr: 7032500
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074010629
El. number:
 Finland 3423422
 Denmark 8212002500
 Italy 7301005
 Sweden 2536103

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:			
mm:	52	50	40
inch:	2	2	1.6
Materials:			
Material:	PC		
Base colour:	RAL 7035		
Cover colour:	RAL 7035		
Cover screws material:	Stainless steel		
Gasket material:	Polyurethane		
Temperatures:			
Short term:	-40 ... 120 °C		
Continuous:	-40 ... 80 °C		
Short term:	-40 ... 250 °F		
Continuous:	-40 ... 175 °F		
Accessories:			
TM 0505	Mounting plate		

Rating:
Ingress Protection (EN 60529): IP 66/67
Impact Resistance (EN 50102): IK 08/07
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
UV resistance: UL 508
Flammability Rating (UL 746 C 5): UL 94 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 12, 13
Certificates:
Underwriters Laboratories
Fimko
Europe EN 50298 1998
Gost R

FIBOX EURONORM II 050504

